



PIN	A	B
2	7.5	2.5
3	10.0	5.0
4	12.5	7.5
5	15.0	10.0
6	17.5	12.5
7	20.0	15.0
8	22.5	17.5
9	25.0	20.0
10	27.5	22.5
11	30.0	25.0
12	32.5	27.5
13	35.0	30.0
14	37.5	32.5
15	40.0	35.0
16	42.5	37.5

Ambient temperature Range $-25^{\circ} \sim +85^{\circ}$
 Applicable Wires :AWG 28#~22#
 Applicable PCboard thickness :0.8mm~1.6mm
 Voltage rating :250V AC,DC
 Current rating :3A
 Contact Resistance $<0.01\Omega$
 Insulation Resistance $>1000M\Omega$
 Withstand Voltage :800V/min
 Material
 1,Pedestal :PA66,UL94V-0
 2,Pins : Brass

2508WV-XXP	PA66 UL94V-0	2508H	2508T
PART-NO	Material	Suitable Housing	Suitable Terminal

_____		new		2015/5/3		A		HAN	
ECN BO.		DESCRIPTION.		DATE.		REV.		Electricity	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	2508WV-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	2508WV-XXP			X.x	±0.20	
							X.xx	±0.15	
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	