

COAXIAL ADAPTER, MCX - N, 75 Ohm, jack / jack (female / female)

31_MCX-N-75-10/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
MCX-75	jack (female)	HUBER+SUHNER-MCX75
N	jack (female)	Not compatible to N 50 Ohms

Interface and material data		
MCX-75		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	75 Ω
Interface frequency	1.5 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 3 GHz	29 dB	1.07

COAXIAL ADAPTER, MCX - N, 75 Ohm, jack / jack (female / female)
31_MCX-N-75-10/133_N

Mechanical data	
Weight	0.0292 kg
Mating cycles	500

Environmental data	
Operation temperature	-55 °C ... 155 °C

Ordering Information Table		
Item number	Item description	Packaging type
22651488	31_MCX-N-75-10/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2406 / Date of publication: 27.05.2024 / uncontrolled copy