


COAXIAL CONNECTOR, SK, 50 Ohm, Straight cable plug (male)

11_SK-50-2-64/119_N

Properties

- The shortened male pin ensures a non-destructive mating process
- Particularly well suited for semi-rigid, semi-flex and flexible cable
- Mechanical intermateable with SMA and PC 3.5 (3.5 mm standard)

**Product configuration**

Interface type	Gender	Standard
SK	plug	MIL-STD-348A/323

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	40 GHz

Mechanical data

Weight	2.8 g
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data

Operation temperature	-40 °C ... 125°C
-----------------------	------------------

COAXIAL CONNECTOR, SK, 50 Ohm, Straight cable plug (male)

11_SK-50-2-64/119_N

Ordering Information Table		
Item number	Item description	Packaging type
85073240	11_SK-50-2-64/119_NE	Single

Suitable cables	
Cable group	Y21 - 2 mm / 50 Ohm
	Y20 - 2 mm / 50 Ohm

Additional Information	
Only as assembly	Yes

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P27563 / Date of publication: 25.11.2023 / uncontrolled copy