







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
A254V12-0B1P51-H25A60	1	0.00	2.54
A254V12-0B2P51-H25A60	2	2.54	5.08
A254V12-0B3P51-H25A60	3	5.08	7.62
A254V12-0B4P51-H25A60	4	7.62	10.16
A254V12-0B5P51-H25A60	5	10.16	12.70
A254V12-0B6P51-H25A60	6	12.70	15.24
A254V12-0B7P51-H25A60	7	15.24	17.78
A254V12-0B8P51-H25A60	8	17.78	20.32
A254V12-0B9P51-H25A60	9	20.32	22.86
.....			
A254V12-0B40P51-H25A60	40	(40-1)X2.54	(40)X2.54

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. A254V12-0BXP51-H25A60	TITLE:2.54PH H2.5 1xnPin 90度 PC3.0 PA6.0 PB4.3 L13.8 6T 第四版		
.XX ±0.20	X.X* ±1°				
.XXX ±0.10	X.XX* ±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1