

SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max




Operation Temperature:-40°to+105°

Insulator Material:Polyester(UL94V-0)

Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
FH1.0-01-01PZD	1	0.00	1.00
FH1.0-01-02PZD	2	1.00	2.00
FH1.0-01-03PZD	3	2.00	3.00
FH1.0-01-04PZD	4	3.00	4.00
FH1.0-01-05PZD	5	4.00	5.00
FH1.0-01-06PZD	6	5.00	6.00
FH1.0-01-07PZD	7	6.00	7.00
FH1.0-01-08PZD	8	7.00	8.00
FH1.0-01-09PZD	9	8.00	9.00
.....			
FH1.0-01-40PZD	40	(PIN-1)	(PIN)

PART NUMBER DESCRIPTION:

FH1.0-01-NPZD

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;01.....40PIN)

(排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:1.0FH H2.0 1xNPin 180度 W1.5 U型 PC2.0 6T	
DECIMALS:	ANGLES:	PAR	FH1.0-01-NPZD
X.±0.30	X°±5'	DWN	
X.X±0.20	X.X°±1'	CHKD	
X.XX±0.10	X.XX°±0.5'	APVD	
CUSTOMER COPY		SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A