




SCHEMATIC



PCB LAYOUT



SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $160\pm 50\text{gf}$
6. Travel: $0.25\pm 0.1\text{mm}$.
7. life test: 10,000 cycles.
8. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.

电话 : 0769-82320511-867

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm:±0.1	ANGULAR	1						
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
5	CONTACT FOOT	BRASS	4	AG-PLATED	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
4	HOUSING	PA6T	1	BLACK	MODEL: TC-06122E-073C				SCALE: 1:1	COMPLIANT	CHK'D		
3	SPRING	PHOSPHOR BRONZE	1	Ag CLAD	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD		PRO.AGL: 		REV : A
2	COAT	SUS	1	NI-PLATED									
1	BUTTON	PA66	1	BLACK									
NO.	PART	NAME	MATERIAL	QTY	FINISHING								