






SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 50m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 160 $\pm$ 50gf.
- 6.Travel: 0.25 $\pm$ 0.1mm.
- 7.life test: 100,000 cycles.
- 8.Operation temperature range: -25 $^{\circ}$ C~85 $^{\circ}$ C.
- 9.Sign "*" is importance dimension.



				TOLERANCE UNLESS SPECIFIED							
6	DUSTPROOF FILM	PI	1	YELLOW	<1.5: $\pm 0.1mm$ >1.5~5.0: $\pm 0.25mm$ >5.0: $\pm 0.3mm$	ANGULAR $\pm 1^{\circ}$	A0	2024.7.9	首次发行	YKH	
5	CONTACT	PHOSPHOR BRONZE	1	Ag-PLATED			NO	DATE	REVISIONS	BY	APPD
4	CASE	LCP	1	BLACK	TITLE: TACT SWITCH		UNIT : MM		ROHS COMPLIANT	DWN	
3	SPRING	SUS	2	Ag-CLAD	MODEL: TS-1134SA-C-03		SCALE: 1:1		CHK'D		
2	COVER	SUS	1	Ag-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司		APPD		PRO.AGL: 		REV :A0
1	BUTTON	LCP	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							