

COAXIAL CONNECTOR, SK, 50 Ohm, Straight bulkhead cable jack (female)

24_SK-50-2-56/199_N

Properties

- The shortened male pin ensures a non-destructive mating process
- Particularly well suited for semi-rigid, semi-flex and flexible cable
- Mechanical intermateable with SMA and PC 3.5 (3.5 mm standard)



Product configuration

Interface type	Gender	Standard
SK	jack	MIL-STD-348A/323

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Stainless Steel	Passivated (Plating)
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	40 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 40 GHz		

Mechanical data

Weight	0.0053 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	soldered

COAXIAL CONNECTOR, SK, 50 Ohm, Straight bulkhead cable jack (female)

24_SK-50-2-56/199_N

Environmental data	
Operation temperature	-40 °C ... 125°C

Ordering Information Table		
Item number	Item description	Packaging type
85020614	24_SK-50-2-56/199_NE	Single

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y16 - 2 mm / 50 Ohm
	U99 - Customer specific
Suitable cables	SR_86_M17
	SUCOFORM_86

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2579 / Date of publication: 25.11.2023 / uncontrolled copy