

Preliminary DATA SHEET

GSM2424: 2300 to 2400MHz High Linearity 24dBm Power Amplifier

Product overview

GSM2424 is a two-stage HBT small cell power amplifier for indoor cellular base stations. It works at 2300~2400 MHz (Band 40). This PA can deliver 24dBm output power with ACPR below -49 dBc and power gain higher than 28dB




Figure 1. 16 Pad 5 x 5 mm Laminate Package

Key Features

- 2300MHz – 2400MHz
- 28dB Gain
- 12% PAE at 24dBm output power
- Below -49dBc ACPR at 24dBm output power w/o DPD
- Input/output internally matched to 50Ohm
- Integrated temperature compensation circuits
- Compact and low-cost 5mm x 5mm LGA package (MSL3, 260°C per JEDEC J-STD-020)
- ESD Level: HBM 1000V; CDM 1000V
- ROHS compatible




Figure 2. GSM2424 Function Block Diagram

Applications

- FDD and TDD 2G/3G/4G LTE systems and 5G NR
- 3GPP Band 40, n40
- Driver amplifier for micro-base and macro-base stations
- Active antenna array and massive MIMO
- Customer Premises Equipment (CPE)

Table 1. Pin-to-Pin Compatible PA Family

Part Num	Frequency (MHz)	3GPP Band
GSM0724	728-821	Bands n12, n20
GSM0824	869-894	Band 5, n5
GSM0924	925-960	Band 8, n8
GSM1824	1805-1880	Band 3, n3
GSM2124	2110-2170	Band 1, n1
GSM2624	2496-2690	Band 41, n41
GSM3524	3300-3600	n78
GSM4024	3700-4000	n77, C Band

Ordering Information

Part No.	Description
GSM2424	2300-2400MHz 24dBm linear PA, 7' Reel with 1500pcs