




SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:
240°C for30-60seconds
(260°C for5seconds)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B100N08-0B1P51-H20C28	1	0.00	1.00
B100N08-0B2P51-H20C28	2	1.00	2.00
B100N08-0B3P51-H20C28	3	2.00	3.00
B100N08-0B4P51-H20C28	4	3.00	4.00
B100N08-0B5P51-H20C28	5	4.00	5.00
B100N08-0B6P51-H20C28	6	5.00	6.00
B100N08-0B7P51-H20C28	7	6.00	7.00
B100N08-0B8P51-H20C28	8	7.00	8.00
B100N08-0B9P51-H20C28	9	8.00	9.00
.....			
B100N08-0B40P51-H20C28	40	(40-1)	40

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE:1.0FH H2.0 1xnPin SMT W1.5 U型 PC2.8 PB2.3 6T (左前右后)	
.XX ±0.20	X.* ±1°	B100N08-0BXP51-H20C28	MANUFACTURE DWG	
.XXX ±0.10	X.XX* ±0.5°	DESIGN: Ethan		
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---		N:A	1/1