





P.C.B LAYOUT



SCHEMATIC



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 1P3T
4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
5. Operating Force: $200\pm 80\text{gf}$, $350\pm 100\text{gf}$
6. Life test: 10,000 cycles

电话 : 0769-82320511-867

KNOB X=2, 3, 4, 5mm

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ±0.1	ANGULAR	A0							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
4	MK23D38 SPRING	PBS	1	NATURAL	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS	DWN				
3	MK23D38 KNOB	PA46/PA9T	1	BLACK	MODEL:MK-13D38G2-B弹线环保			SCALE: 6:1	COMPLIANT	CHK'D				
2	MK23D38 COVER	0.2mm SUS	1	WASHING	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
1	MK13D38(C) CASE	PA9T/9# BRASS STRIP	1	BLACK/Ag PLATED										
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO.AGL:	 	REV :A0