






SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ C to +105 $^{\circ}$ C
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240 $^{\circ}$ C for 30-60 seconds
(260 $^{\circ}$ C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B200M02-0B2P51-H64C28	2*1	0.00	2.00
B200M02-0B4P51-H64C28	2*2	2.00	4.00
B200M02-0B6P51-H64C28	2*3	4.00	6.00
B200M02-0B8P51-H64C28	2*4	6.00	8.00
B200M02-0B10P51-H64C28	2*5	8.00	10.00
B200M02-0B12P51-H64C28	2*6	10.00	12.00
B200M02-0B14P51-H64C28	2*7	12.00	14.00
B200M02-0B16P51-H64C28	2*8	14.00	16.00
B200M02-0B18P51-H64C28	2*9	16.00	18.00
.....			
B200M02-0B80P51-H64C28	2*40	(40-1)x2.0	(40)x2.0

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	± 0.30	X.*	$\pm 5^{\circ}$	PART NO.	TITLE: 2.0FH H6.35 2xnPin
.XX	± 0.20	X.X*	$\pm 1^{\circ}$	B200M02-0BXP51-H64C28	180度 Y型 PC2.8 6T
.XXX	± 0.10	X.XX*	$\pm 0.5^{\circ}$	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---		SCALE	SHEET	
			N:A	1/1	