





SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors



Series 802 replacement flange gaskets, o-rings and piston rings

FLANGE GASKETS FOR SERIES 802 MIGHTY MOUSE RECEPTACLES


These flange gaskets provide sealing between square flange receptacles and the mounting panel. Choose fluorosilicone, Viton, or neoprene material. Gaskets are .032" (0.8) thick.



Shell Size	Part Number			Dimensions				
	Fluorosilicone	Viton®	Neoprene	A Bsc.	B Dia.	C Typ.	D Dia.	E Rad.
5	809-108F51	809-108V51	809-108N51	.500 (12.70)	.448 (11.38)	.885 (22.48)	.125 (3.18)	.105 (2.67)
6	809-108F52	809-108V52	809-108N52	.625 (15.88)	.572 (14.53)	1.010 (25.65)	.125 (3.18)	.105 (2.67)
7	809-108F53	809-108V53	809-108N53	.688 (17.48)	.635 (16.13)	1.072 (27.23)	.125 (3.18)	.105 (2.67)
8	809-108F54	809-108V54	809-108N54	.750 (19.05)	.698 (17.73)	1.135 (28.83)	.125 (3.18)	.105 (2.67)
9	809-108F55	809-108V55	809-108N55	.812 (20.62)	.760 (19.30)	1.195 (30.35)	.125 (3.18)	.105 (2.67)
10	809-108F56	809-108V56	809-108N56	.875 (22.23)	.822 (20.88)	1.260 (32.00)	.125 (3.18)	.105 (2.67)
12	809-108F57	809-108V57	809-108N57	.938 (23.83)	.885 (22.48)	1.323 (33.60)	.125 (3.18)	.105 (2.67)
14	809-108F58	809-108V58	809-108N58	1.125 (28.58)	1.072 (27.23)	1.510 (38.35)	.125 (3.18)	.105 (2.67)
15	809-108F59	809-108V59	809-108N59	1.188 (30.18)	1.135 (28.83)	1.573 (39.95)	.125 (3.18)	.105 (2.67)
21	809-108F60	809-108V60	809-108N60	1.375 (34.92)	1.448 (36.78)	1.760 (44.70)	.125 (3.18)	.105 (2.67)


802 REPLACEMENT O-RINGS FOR MIGHTY MOUSE RECEPTACLES

These Viton® O-rings fit Series 802 "AquaMouse" rear panel mount jam nut connector flanges.



Flange O-rings for Series 802 Jam Nut and Square Flange Receptacles						
Shell Size	Jam Nut Flange Style			Square Flange Style		
	Viton® Part No.	O-Ring Size	Ø A Inside Dia.	Viton® Part No.	O-Ring Size	Ø A Inside Dia.
-05	809-165-05	2-015	.551 (14.00)	809-165-35	2-012	.364 (9.25)
-06	809-165-06	2-017	.676 (17.17)	809-165-36	2-014	.489 (12.42)
-07	809-165-07	2-018	.739 (18.77)	809-165-37	2-015	.551 (14.00)
-08	809-165-08	2-019	.801 (20.35)	809-165-38	2-016	.614 (15.60)
-09	809-165-09	2-020	.864 (21.95)	809-165-39	2-017	.676 (17.17)
-10	809-165-10	2-021	.926 (23.52)	809-165-40	2-018	.739 (18.77)
-12	809-165-12	2-022	.989 (25.12)	809-165-42	2-019	.801 (20.35)
-14	809-165-14	2-025	1.176 (29.87)	809-165-44	2-022	.989 (25.12)
-15	809-165-15	2-026	1.239 (31.47)	809-165-45	2-023	1.051 (26.70)
-21	809-165-21	2-030	1.614 (41.00)	809-165-51	2-028	1.364 (34.65)

These Viton® Piston O-rings fit Series 802 "AquaMouse".



Piston O-rings for Series 802							
Shell Size	Viton® Part No.	O-Ring ID x Width Dimensions		Shell Size	Viton® Part No.	O-Ring ID x Width Dimensions	
		In.	mm.			In.	mm.
-05	809-209-05	.208 x .070	5.28 x 1.78	10	809-209-10	.551 x .070	14.00 x 1.78
-06	809-209-06	.270 x .070	6.86 x 1.78	12	809-209-12	.614 x .070	15.60 x 1.78
-07	809-209-07	.364 x .070	9.24 x 1.78	14	809-209-14	.801 x .070	20.34 x 1.78
-08	809-209-08	.384 x .070	9.75 x 1.78	15	809-209-15	.864 x .070	21.94 x 1.78
-09	809-209-09	.489 x .070	12.42 x 1.78	21	809-209-21	1.051 x .070	26.70 x 1.78



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[809-165-12](#) [809-209-12](#) [809-165-40](#) [809-209-06](#) [809-209-10](#) [809-209-14](#) [809-209-09](#)