

COAXIAL CONNECTOR, UHF, other Ohm, Straight cable plug (male)  
11\_UHF-0-7-5/002\_-

**Properties**

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz



| Product configuration |        |              |
|-----------------------|--------|--------------|
| Interface type        | Gender | Standard     |
| UHF                   | plug   | IEC 60169-12 |

| Interface and material data |            |                |
|-----------------------------|------------|----------------|
| Piece parts                 | Material   | Plating        |
| Centre contact              | Brass      | Silver Plating |
| Outer conductor             | Brass      | Silver Plating |
| Body                        | Brass      | Silver Plating |
| Insulator                   | PFA / PTFE |                |
| Coupling nut                | Brass      | Nickel Plating |

| Electrical data     |         |
|---------------------|---------|
| Interface frequency | 0.2 GHz |

| Mechanical data            |           |
|----------------------------|-----------|
| Weight                     | 0.0236 kg |
| Mating cycles              | 500       |
| Cable entry centre contact | soldered  |
| Cable entry outer contact  | others    |

| Environmental data    |                  |
|-----------------------|------------------|
| Operation temperature | -55 °C ... 165°C |

| Ordering Information Table |                     |                |
|----------------------------|---------------------|----------------|
| Item number                | Item description    | Packaging type |
| 22542733                   | 11_UHF-0-7-5/002_-E | Single         |

**COAXIAL CONNECTOR, UHF, other Ohm, Straight cable plug (male)**  
11\_UHF-0-7-5/002\_-

| Suitable cables        |                     |
|------------------------|---------------------|
| Cable group            | U29 - 7 mm / 50 Ohm |
| Suitable cables        | RG_213_/U           |
| Additional Information |                     |
| Only as assembly       | No                  |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P3355 / Date of publication: 25.11.2023 / uncontrolled copy