

COAXIAL ADAPTER, BNC - SMA, 50 Ohm, plug / jack (male / female)

33_BNC-SMA-50-1/1--_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
BNC	plug (male)	IEC 61169-8_MIL-STD-348A/301_CEEC 22120
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CEEC 22110

Interface and material data

BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 4 GHz		

COAXIAL ADAPTER, BNC - SMA, 50 Ohm, plug / jack (male / female)
33_BNC-SMA-50-1/1--_N

Mechanical data	
Weight	0.0119 kg
Mating cycles	500

Ordering Information Table		
Item number	Item description	Packaging type
22652906	33_BNC-SMA-50-1/1--_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2240 / Date of publication: 27.05.2024 / uncontrolled copy