

COAXIAL ADAPTER, N - 7/16, 50 Ohm, plug / jack (male / female)

33_N-716-50-1/---_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N	plug (male)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
N		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
7/16		
Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz
VSWR	DC - 7.5 GHz ($\leq 1.03 + 0.02 f \text{ GHz}$)

COAXIAL ADAPTER, N - 7/16, 50 Ohm, plug / jack (male / female)
33_N-716-50-1/---_U

Mechanical data		
Weight	0.1015 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22641229	33_N-716-50-1/--_UE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2215 / Date of publication: 27.05.2024 / uncontrolled copy