

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1054292314

Status:


Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Dual Row, 14 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-105405-001-001 (PDF)

Application Specification AS-105405-001-001 (PDF)

Packaging Specification 1054291000-PK-000 (PDF)

Test Summary 1054050000-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	105429
Application	Power, Wire-to-Board
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	191130013623
Physical	
Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Natural
Durability (mating cycles max)	50
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.750/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Temperature Range - Operating	-40° to +115°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-105405-001-001
Packaging Specification	1054291000-PK-000
Product Specification	PS-105405-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -ED/88/2018 (15 January 2019)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

105429 Series

Mates With

Nano-Fit Receptacle Housing 105308

Use With

Nano-Fit Crimp Terminal 105300

This document was generated on 04/23/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION