

零件承认书

SPECIFICATION FOR APPROVAL

客户名称: 001

增益型号: ZEAL0410-102

规格描述: 色环电感0410 1mH 10% 110mA 编带

日期: 2022/6/11

版本: A

增益签核:

制订	审核	核准
夏琳		李万

客户签核:

工程	审核	核准



东莞市增益实业有限公司

地址: 东莞市塘厦镇林村塘厦大道北552号

电话: 0769-87321000

传真: 0769-87891229

物料类型: 色环电感


日期: 2022/6/11

版本: A

东莞市增益实业有限公司
Dongguan ZengYi Industrial Co., LTD.


CUSTOMER		MADE	
MODEL No.		DATE	2022-6-11
PART No.	ZEAL0410-102	PAGE	1
DESCRIPTION	FIXED INDUCTORS	REVISION	A

1、 SHAPE & DIMENSION (UNIT: m/m)



C1	棕色	C2	黑色	C3	红色	C4	银色
A	10.0MAX	D					
B	4.0MAX	E	0.6±0.1				
C	62±2	F					

2. ELECTRICAL SCHEMATICS



Tel: 0769-87321000

Fax: 0769-87891229

地址: 东莞市塘厦镇林村塘厦大道北 552 号

东莞市增益实业有限公司
Dongguan ZengYi Industrial Co., LTD.

CUSTOMER		MADE	
MODEL No.		DATE	2022-6-11
PART No.	ZEAL0410-102	PAGE	2
DESCRIPTION	FIXED INDUCTORS	REVISION	A

3.ELECTRICAL SPECIFICATION & TEST INSTRUMENTS

MEAS. ITEM	L	Q	DCR	RatedDCCurrent	
UNIT	mH		Ω	mA	
SPEC	1.0 \pm 10%	50Min	14Max	110	
TEST FREQ	1KHz/0.25V	0.796MHz/1V			
TEST STRUMENTS	HP-4285A	HP-4285A	502BC		

4.MATERIAL LIST

No	ITEM	Material		Vendor	Rating	UL File	ROHSstate
1	CORE	FC1 3 \times 6	FCI	HENGCI	150 $^{\circ}$ C		Yes
2	WIRE WINDING	2UEW Φ 0.07mm	URNS:248 Ts (REF)	HOILUEN	130 $^{\circ}$ C	EI64409	Yes
3	EPOXY RESIN	NC-G		homeTown	200 $^{\circ}$ C		Yes
4	PNI	Φ 0.6	CP	BAI CHUAN	130 $^{\circ}$ C		Yes

或同等材质供应商

※REMARK※

Tel: 0769-87321000

Fax: 0769-87891229

地址: 东莞市塘厦镇林村塘厦大道北 552 号

东莞市增益实业有限公司
Dongguan ZengYi Industrial Co., LTD.

CUSTOMER		MADE	
MODEL No.		DATE	2022-6-11
PART No.	ZEAL0410-102	PAGE	3
DESCRIPTION	FIXED INDUCTORS	REVISION	A

5. TEST DATA FOR PREPRODUCTION SAMPLE

MEAS.ITEM	L (mH)	Q	DCR (Ω)
SPEC	1.00±10%	50MIN	14.0MAX
1	1.01	60	11.4
2	1.01	61	11.1
3	0.99	58	11.5
4	1.01	58	11.5
5	1.02	63	11.8
6	1.01	62	11.5
7	1.00	57	11.8
8	1.01	62	11.4
9	1.03	58	11.6
10	1.01	60	11.4
\bar{x}			
R			
YOUR SAMPLE			

TEST CONDITION: TEMP: 25°C(REF.) R.H.: 60%(REF.)

Tel: 0769-87321000

Fax: 0769-87891229


地址: 东莞市塘厦镇林村塘厦大道北 552 号

东莞市增益实业有限公司
Dongguan ZengYi Industrial Co., LTD.

CUSTOMER		MADE	
MODEL No.		DATE	2022-6-11
PART No.	ZEAL0410-102	PAGE	4
DESCRIPTION	FIXED INDUCTORS	REVISION	A

6.RELIABILITY TEST METHOD

6-1. MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Terminal pull strength	9.8(N)MIN	A pulling load should be gradually applied to the leads in a downward direction and should be monitored the value at the point of destroy.
Terminal bending strength	1CYCLE MIN	A specified load of 4.9(N) should be suspended, From the terminal then slowly inclined the 90°C, and then return to normal position ,The consecutive bends shall be done in the opposite directions.(Total 1 cycle)
Dropping	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 20\%$ There is no evidence of any mechanical failures	The sample shall be dropped on a concrete floor once from 1 meter height (39 inches) Total 3 cycles.
Vibration	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 20\%$ There is no evidence of any mechanical failures	
Resistance to soldering heat	There is no evidence of any mechanical failures	The sample should be immersed to a depth of 1.5mm below the lower core surface into solder at a temperature of 260°C (+10,-0)for a duration of 5seconds(+1,-0).

6-2.ELECTRICAL

TEST ITEM	SPECIFICATION
Insulation Resistance	The insulation resistance between core to coil is over 100MΩ at500V, 3SEC.
Withstand Voltage	Apply AC 500V between core to coil for one minute there shall not be any abnormality.

Tel: 0769-87321000

Fax: 0769-87891229

地址: 东莞市塘厦镇林村塘厦大道北 552 号

东莞市增益实业有限公司
Dongguan ZengYi Industrial Co., LTD.

CUSTOMER		MADE	
MODEL No.		DATE	2022-6-11
PART No.	ZEAL0410-102	PAGE	5
DESCRIPTION	FIXED INDUCTORS	REVISION	A

6-3. ENVIROMENT CHARACTERISTICS

TEST ITEM	SPECIFICATION	TEST DETAILS
High temperature storage	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 25\%$ There is no evidence of any mechanical failures	The coil should be stored at an ambient temperature of $+85 \pm 2^\circ\text{C}$ for 72 hours ,after which the measurement should be made.
Low temperature storage	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 25\%$ There is no evidence of any mechanical failures	The coil should be stored at an ambient temperature of $-40 \pm 2^\circ\text{C}$ for 500 hours ,after which the measurement should be made.
Thermal shock	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 30\%$ There is no evidence of any mechanical failures	
Humidity life test	$\Delta L/L0 \leq \pm 5\%$ $\Delta Q/Q0 \leq \pm 30\%$ There is no evidence of any mechanical failures	The rated current shall be applied to the coil at an ambient temperature $+40 \pm 2^\circ\text{C}$ with relative humidity of 90% for 1000 hours.

6-4. SAFETY

TEST ITEM	SPECIFICATION	TEST DETAILS
Over load test	No abnormal smoking or fire	The twice current of the rated dc current should be applied to the coil for 5 min

Tel: 0769-87321000

Fax: 0769-87891229

地址: 东莞市塘厦镇林村塘厦大道北 552 号