







Section A-A

N = Number of poles

Dim A = $N \times 5.08 + 1.0$

Dim B = $(N - 1) \times 5.08$

Dim C = $N \times 5.08 + 2.1$

	Dim A	Dim B	Dim C
2-6p	±0.10	±0.15	±0.15
7-12p	±0.20	±0.20	±0.20
13-16p	±0.30	±0.25	±0.25
17-24p	±0.40	±0.35	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item : Terminal housing: Thermoplastic (UL94 V-0)
- Item : Hexagon nut : Brass , M2.5

Electrical (Match with AR series)

- Voltage rating: 300V
- Current rating: 10A
- Wire range: 1.5 ~ 2.5mm²
- Withstanding Voltage: 1.6KV

KV xx 50 x 2 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

... 24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)

G: Pb < 40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KV 5.08 SERIES (Flange With Nut & Low profile)					
PART NO.		KVxx50x2xxxxG			DWG NO.		8KV0003
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Kind	Kind				
		2009.12.15	2009.08.10		SHEET: 01/01	UNIT: mm	X. ±0.50
						SCALE: 2/1	X.X ±0.30
						REV.: B	X.XX ±0.10
							X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KV0250520000G</u>	<u>KV0350520000G</u>	<u>KV0450520000G</u>	<u>KV0550520000G</u>	<u>KV0650520000G</u>	<u>KV0750520000G</u>
<u>KV0850520000G</u>	<u>KV0950520000G</u>	<u>KV1050520000G</u>	<u>KV1150520000G</u>	<u>KV1250520000G</u>	<u>KV1350520000G</u>
<u>KV1450520000G</u>	<u>KV1550520000G</u>	<u>KV1650520000G</u>	<u>KV1750520000G</u>	<u>KV1850520000G</u>	<u>KV1950520000G</u>
<u>KV2050520000G</u>	<u>KV2150520000G</u>	<u>KV2250520000G</u>	<u>KV2350520000G</u>	<u>KV2450520000G</u>	