

SANYO Semiconductors **DATA SHEET**

LB11963T — For Fan Motor Single-phase Full-wave

Overview

The LB11963T is a single-phase bipolar drive fan motor driver. Incorporating 1/2 FG output for 8-pole fan motors in a miniature MSOP8 package, it is optimum for driving compact fan motors used in the notebook PC.

This IC is pin-compatible to the LB11964T with normal FG output, and a common circuit board can be used for both 4-and 8-pole motors.

Functions

- Single-phase full-wave drive
- The built-in regeneration circuit makes it possible to use a reverse connection prevention diode.
- 1/2FG output
- Built-in thermal protection circuit

Specifications

Absolute Maximum Ratings at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Supply voltage	V _{CC} max		15	V
Output current	IOUT max		0.5	Α
Output voltage	V _{OUT} max		15	V
FG output withstand voltage	VR max	/ /	15	V
FG output current	IR max		5	mA
Allowable power dissipation	Pd max	Specified substrate *	400	mW
Operating temperature range	Topr		-30 to 85	°C
Storage temperature	Tstg		-55 to 150	°C

^{*} Specified substrate: 20mm×10mm×0.8mm, paper phenol, wiring density 20%.

- Any and all SANYO Semiconductor Co.,Ltd. products described or contained herein are, with regard to "standard application", intended for the use as general electronics equipment (home appliances, AV equipment, communication device, office equipment, industrial equipment etc.). The products mentioned herein shall not be intended for use for any "special application" (medical equipment whose purpose is to sustain life, aerospace instrument, nuclear control device, burning appliances, transportation machine, traffic signal system, safety equipment etc.) that shall require extremely high level of reliability and can directly threaten human lives in case of failure or malfunction of the product or may cause harm to human bodies, nor shall they grant any guarantee thereof. If you should intend to use our products for applications outside the standard applications of our customer who is considering such use and/or outside the scope of our intended standard applications, please consult with us prior to the intended use. If there is no consultation or inquiry before the intended use, our customer shall be solely responsible for the use.
- Specifications of any and all SANYO Semiconductor Co.,Ltd. products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

Recommended Operating Ranges at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Supply voltage	Vcc		3.5 to 13.8	V
Hall input common-mode input voltage range	VICM		0.2 to V _{CC} -1.5	V


Electrical Characteristics at Ta = 25°C, $V_{CC} = 5V$, unless otherwise specified.


Parameter	Cumple of	Conditions	Ratings			
Parameter	Symbol	Conditions	min	typ	max	unit
Circuit current	Icc	During rive (CT=L)		9.0	14	mA
		During lock protection (CT=H)		3.0	5.0	mA
Charge current of lock detection capacitor	I _{CT} 1	V _{CT} =0.2V	1.1	1.8	2.6	μΑ
Capacitor discharge current	I _{CT} 2	V _{CT} =3.2V	0.15	0.25	0.40	μА
Capacitor charge/discharge ratio	R _{CT}	RCD=ICT1/ICT2	5.0	7.0	9.0	
CT charge voltage	V _{CT} 1		2.6	2.9	3.2	V
CT discharge voltage	V _{CT} 2		1.5	1.8	2.1	V
Output L voltage	V _O L	I _O =200mA		0.2	0.3	V
Output H voltage	V _O H	I _O =200mA	3.9	4.1		V
Hall input sensitivity	VHN	Zero peak value		7/	15	mV
(including offse		(including offset and hysteresis)		` //		
FG output L voltage	VRD	IRD=5mA		0.1	0.3	V
FG output leak current	IRDL	VRD=7V			30	μΑ
Thermal protection circuit	TSD	* Design target value	150	180	210	°C

^{*:} Design target value and no measurement was made.


Package Dimensions

unit : mm (typ) 3245B





Pin Assignment




Truth Table

IN+	IN-	СТ	OUT1	OUT2	FG	Mode
Н	L	L	L	Н	*4	Datas
L	Н	L	Н	L	^1	Rotation
-	-	Н	OFF	OFF	H (*2)	During lock protection
-	-	-	OFF	OFF	-	Overheat protection

- *1 FG equivalent to 1/2 of the frequency corresponding to the phase changeover is output. Accordingly, the same FG output frequency is available for both eight-pole and four-pole motors. This is compatible with pins of LB11964T that is the FG output compatible with four poles.
- *2 In the restart mode (output ON) during rotor restriction, the FG output causes an operation similar to the one during rotation and varies depending on the rotor position.

Application Circuit Example



- *1 This is Di to prevent breakage due to reverse connection. The built-in regeneration circuit regenerates the coil current between lower NPN outputs, suppressing kickback.
 - This may be eliminated if there is no problem because a power connector, etc. is used.
- *2 This is necessary for commutation when the rotation speed is to be controlled with power PWM.
- *3 Must be left open when not used.
- *4 Chattering preventive measure is taken for the FG output by providing the Hall amplifier with hysteresis and by ensuring the pin arrangement with less interference. It is essential to carry out short wiring to make carrying of noise difficult.



- SANYO Semiconductor Co.,Ltd. assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all SANYO Semiconductor Co.,Ltd. products described or contained herein.
- SANYO Semiconductor Co.,Ltd. strives to supply high-quality high-reliability products, however, any and all semiconductor products fail or malfunction with some probability. It is possible that these probabilistic failures or malfunction could give rise to accidents or events that could endanger human lives, trouble that could give rise to smoke or fire, or accidents that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all SANYO Semiconductor Co.,Ltd. products described or contained herein are controlled under any of applicable local export control laws and regulations, such products may require the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written consent of SANYO Semiconductor Co.,Ltd.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the SANYO Semiconductor Co.,Ltd. product that you intend to use.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.
- Upon using the technical information or products described herein, neither warranty nor license shall be granted with regard to intellectual property rights or any other rights of SANYO Semiconductor Co.,Ltd. or any third party. SANYO Semiconductor Co.,Ltd. shall not be liable for any claim or suits with regard to a third party's intellectual property rights which has resulted from the use of the technical information and products mentioned above.

This catalog provides information as of May, 2007. Specifications and information herein are subject to change without notice.