

A 4 -18 - Ferrule



3202834

<https://www.phoenixcontact.com/us/products/3202834>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, sleeve length: 18 mm, color: silver

Your advantages

- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper
- The A 0,25.. ferrules can also be used to process 0.14 mm² conductors

Commercial data

Item number	3202834
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BH34
Product key	BH3412
Catalog page	Page 480 (C-3-2019)
GTIN	4017918171438
Weight per piece (including packing)	0.3 g
Weight per piece (excluding packing)	0.3 g
Customs tariff number	85369010
Country of origin	DE

A 4 -18 - Ferrule

3202834

<https://www.phoenixcontact.com/us/products/3202834>



Technical data

Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M

Data management status


Article revision	05
------------------	----

Connection data

Conductor connection

Conductor cross section flexible max.	4 mm ²
Conductor cross section AWG max.	12
Stripping length	18 mm

Dimensions

Dimensional drawing	
Sleeve length	18 mm
Maximum stripping length	18 mm
Ferrule diameter	2.8 mm
Sleeve wall thickness	0.2 mm
Inner dimensions of the insulating collar	4 mm

Material specifications

Color	silver-colored
Material	CU-DHP
Coating	tin-plated (galvanic)
Surface characteristics	Tin-plated

Mechanical properties

Technical data

Sleeve length	18 mm
---------------	-------

Environmental and real-life conditions

Ambient conditions

Permanent temperature	105 °C
Short-term temperature	120 °C

Standards and regulations

A 4 -18 - Ferrule

3202834

<https://www.phoenixcontact.com/us/products/3202834>



Design according to standard	DIN 46228-1, UL 486F-A
------------------------------	------------------------

A 4 -18 - Ferrule


3202834

<https://www.phoenixcontact.com/us/products/3202834>



Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

A 4 -18 - Ferrule

3202834

<https://www.phoenixcontact.com/us/products/3202834>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3202834>



cULus Listed

Approval ID: E488001

A 4 -18 - Ferrule



3202834

<https://www.phoenixcontact.com/us/products/3202834>

Classifications

ECLASS

ECLASS-11.0	27400201
ECLASS-13.0	27400201
ECLASS-12.0	27400201

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

A 4 -18 - Ferrule



3202834

<https://www.phoenixcontact.com/us/products/3202834>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com