

SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors

660-088 and 660-087 IP68 Protective cover



Protect Connectors From Damage –

These covers prevent ingress of water and contamination. Stainless steel plug covers feature Viton® O-rings for IP68 sealing (one meter for one hour). Receptacle covers have a Viton® gasket and are made from marine bronze to minimize galling. Cover is designed for low PSI connector protection. For 3500 PSI protection, use part numbers 667-241 and 667-242

Three Types of Attachment Rings

Choose small diameter eye fittings for panel attachment. Larger rings fit under

the jam nut or over cable jackets. Split rings can be installed on fully assembled cables.

Polyurethane-Coated SST Wire Rope

offers high strength, excellent abrasion resistance and good flexibility. Or, choose Fluoropolymer jacket for high temperature exposure.

Braided Nylon Rope

provides excellent flexibility and good abrasion resistance, and can be ordered with slip knot fittings for easy installation on any size cable.




SUBSEA/SALLOW WATER: AQUAMOUSE™

How To Order						
Sample Part Number		667-088	-9	G	04	-6 B
Series (See Table I)	660-088 = Receptacle Cover 660-087 = Plug Cover					
Shell Size	-5, -6, -7, -8, -9, -10, -12, -14, -15, -21					
Attachment Type	G = Nylon Rope H = SST Wire Rope, Fluoropolymer Jacket N = No Attachment S = SST Sash Chain SK = Nylon Rope With Slip Knot T = SST Wire Rope, No Jacket U = SST Wire Rope, Polyurethane Jacket "SST" = Stainless Steel					
Attachment Code (See Table II)	Small Ring = 01, 02, 04, 06 Solid Ring = 16 thru 24 Split Ring = 50 thru 72					
Attachment Length (inches)	Example "-6" equals six inch length Omit for attachment Type N (No Attachment)					
Alternate Key Position (660-087 Only)	Omit for plug connectors with standard "A" key position, for all other positions indicate B, C or D Omit if ordering 660-088 receptacle cover					


Table I: Cover Style	
660-088 Receptacle Cover	660-087 Plug Cover

SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors

660-088 and 660-087 IP68 Protective cover



660-087 Plug Cover



660-088 Receptacle Cover

660-087 & -088 Dimensions




Shell Size	A Hex		B Thread Class 2A	Ø C Max.		D Thread Class 2B
	In.	mm.		In.	mm.	
5	.500	12.70	.438-28 UNEF	.59	15.0	.438-28 UNEF
6	.625	15.88	.562-20 UN	.72	18.3	.562-20 UN
7	.688	17.48	.625-20 UN	.78	19.8	.625-20 UN
8	.750	19.05	.687-20 UN	.84	21.3	.687-20 UN
9	.812	20.62	.750-20 UNEF	.90	22.9	.750-20 UNEF
10	.875	22.23	.812-20 UNEF	.97	24.6	.812-20 UNEF
12	.938	23.83	.875-20 UNEF	1.03	26.2	.875-20 UNEF
14	1.125	28.58	1.062-20 UN	1.22	31.0	1.062-20 UN
15	1.188	30.18	1.125-20 UN	1.28	32.5	1.125-20 UN
21	1.562	39.67	1.438-20 UN	1.61	40.9	1.438-20 UN

NOTES

Materials and Finishes

- Plug Cover: 316 stainless steel, passivated
- Receptacle Cover: marine bronze, unplated
- O-Ring: Viton rubber
- Gasket: Viton rubber
- Wire, Hardware: Stainless steel, passivated

Table II: Attachment Options

	Attch. Code	Screw Size	Ring I.D.	
			In.	mm.
 Small Ring For Attaching Receptacle Covers to a Panel with a Screw	01	#4, M3	.126	3.20
	02	#6	.145	3.68
	04	#8, M4	.188	4.78
	06	#10	.197	5.00
 Solid Ring for Attaching Receptacle Covers to Jam Nut Receptacles	Attch. Code	Receptacle Cover Shell Size	Ring I.D.	
			In.	mm.
	16	5	.570	14.5
	17	6	.635	16.1
	18	7	.695	17.7
	19	8, 9, 10	.885	22.5
	20	12	1.070	27.2
	21	14	1.135	28.8
 Large Split Ring for Attaching Covers to Cables	Attch. Code	Max. Cable Dia.	Min. ID	
			In.	mm.
	50	.410	.420	10.67
	52	.470	.480	12.19
	54	.625	.635	16.13
	56	.735	.745	18.92
	58	.875	.885	22.48
	60	1.000	1.010	25.65
	64	1.115	1.125	28.58
	68	1.335	1.345	34.16
	72	1.416	1.438	36.53
 Slip Knot (SK) for Attaching Covers to Cable				

Jam Nut Major Diameter Thread Reference

Shell Size	Jam Nut Thread Major Dia.	Shell Size	Jam Nut Thread Major Dia.
5	.5000	10	.8750
6	.6250	12	.9375
7	.6875	14	1.1250
8	.7500	15	1.1875
9	.8125	21	1.5000



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[660-088-7N](#) [660-088-9N](#) [660-087-6N](#) [660-088-8N](#) [660-088-5N](#) [660-088-6N](#) [660-088-12N](#) [660-087-9N](#) [660-087-12N](#) [660-087-15H20-4](#) [660-087-7U15-5](#) [660-087-8H16-4](#) [660-088-14U04-5](#) [660-088-8H01-4](#)