



368589-6 Product Details



368589-6

TE Internal Number: 368589-6

Active

Power Double-Lock Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Wire-to-Panel, Wire-to-Wire
- Applies To Panel, Applies To Wire/Cable
- Connector
- Housing
- Connector Style = Receptacle

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [PDL 4P CAP HSG 3.96mm D/R P/M \(GWT\) \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- Wire/Cable Type = Discrete Wire
- Sealed = No

Mechanical Attachment:

- Mating Retention Type = Latching
- Panel Mount Retention = With
- Panel Mount Retention Type = Latch(es)

Electrical Characteristics:

- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 300

Termination Features:

- Termination Method to Wire/Cable = Crimp

Dimensions:

- Panel Thickness (mm [in]) = 0.80 – 2.00 [0.031 – 0.078]

Body Features:

- Wire Type = Stranded
- Mating Retention = With

Contact Features:

- Contact Type = Tab
- Contact Layout = Matrix

Housing Features:

- Connector Style = Receptacle
- Centerline, Matrix (mm [in]) = 3.96 x 4.6 [.156 x .181]

Configuration Features:

- [Number of Positions](#) = 4
- Number of Rows = 2
- [Number of Double-Lock Plates Required](#) = 2

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Agency/Standard = CNR, USR
- UL File Number = UL 1977, C22.2 No. 182.3
- UL Flammability Rating = UL 94V-2

Environmental:

- Operating Temperature (°C [°F]) = 65 [149]

Conditions for Usage:

- Applies To = Panel, Wire/Cable
- Glow Wire Rating = Glow Wire
- For Use With = Double Lock Plate 368590-1, Contacts: 177916 or 177917, Plug (GWT): 368575

Operation/Application:

- Application Use = Wire-to-Panel, Wire-to-Wire
- Contact Transmits (Typical Application) = Signal (Data)/Power

Other:

- Brand = TE Connectivity

- Housing Material = PA66
- Housing Color = Blue
- Mating Alignment = With
- Mating Alignment Type = Polarization

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

