

COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)

16_N-50-6-14/12-_N

Properties

- Suitable for use with Eacon_6C cable
- Applicable in frequencies up to 11 GHz
- Compliant with MIL-STD-348A/304 interface standard

**Product configuration**

Interface type	Gender	Standard
N	plug	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 6 GHz	21.7 dB	1.18
6.01 GHz ... 11 GHz	19.1 dB	1.25

Mechanical data

Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)
16_N-50-6-14/12-_N

Environmental data		
Operation temperature	-60 °C ... 165 °C	
Ingress protection (IP Rating)	Mated / IP67	
Ordering Information Table		
Item number	Item description	Packaging type
85074231	16_N-50-6-14/12-_NE	Single
Suitable cables		
Cable group	U96 - EACON_6C	
Suitable cables	EACON_6C	
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3081 / Date of publication: 17.07.2024 / uncontrolled copy