

SENCITY® Rail Antenna with GPS

87010011

Properties

- Railway rooftop antenna for 1800/1900/UMTS/LTE/ WiFi 1/Wi-Fi 3 band
- Multiple Antenna installations support Cellular and Wi-Fi MIMO
- Embedded GPS antenna (requires separate LNA such as 86010142)
- Rugged design, meets EN 50155 Railway Standard
- Fire retardant acc. to EN 45545-2
- Works also on non-metallic surfaces



Electrical bands				
	Band 1	Band 2	Band 3	Band 4
Name				
Frequency	1710 MHz ... 1920 MHz	1920 MHz ... 2600 MHz	2600 MHz ... 3200 MHz	3200 MHz ... 3800 MHz
VSWR	1.7	1.5	1.6	1.5
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
Gain	7 dBi	6.5 dBi	5.5 dBi	7 dBi
Isolation between Ports				
Ambient Temperature	25 °C	25 °C	25 °C	25 °C

	Band 5
Name	GPS
Frequency	1574.4 MHz ... 1576.4 MHz
VSWR	2
Impedance	50 Ω
Gain	6 dBi
Isolation between Ports	-10 dB
Ambient Temperature	25 °C

Electrical remarks

Remarks	Indicated VSWR values are valid for a metallic ground plane of 500mm x 500mm or larger.
---------	---

SENCITY® Rail Antenna with GPS

87010011

Ports		
	Port 1	Port 2
Port name	Cell / WiFi	GPS
Connector	N, jack (female)	TNC, plug (male)
Polarization	vertical	circular right
DC grounded	Yes	Yes

Connections		
Port number	Port 1	Port 2
Band 1	✓	
Band 2	✓	
Band 3	✓	
Band 4	✓	
Band 5		✓

Mechanical data	
Weight	0.45 kg
Dimensions	81 mm x 145 mm x 85 mm (Height x Width x Depth)
	Wind load: frontal: 0.5 N, lateral: 0.05 N at 600 km/h
	Packaging size (outside): 152 x 91 x 125 mm
Remarks	Radiator: Copper and brass. Flange: Anodized Aluminum. All screws and nuts: Stainless steel. Color: Grey. Sealing: Neoprene and silicon


Interface and material data	
Radome material	Fiberglass
Radome colour	Grey
Back plate/base plate material	Aluminium
Back plate/base plate colour	Black

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP66
Flammability rating	EN 45545-2

Environmental remarks
Environmental tests: EN 50155:2018-05

SENCITY® Rail Antenna with GPS
87010011

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1232 / Date of publication: 10.06.2024 / uncontrolled copy