

SENCITY® Road

1399.99.0177

Properties

- Supports TETRA, Wifi 2.4/5 GHz, Wifi 6E and GNSS (Beidou, Galileo, GPS, Glonass)
- Offers a stick antenna socket and separate connector for each application
- Single hole mounting, easy cabling feed-through



Electrical bands				
	Band 1	Band 2	Band 3	Band 4
Name				GNSS
Frequency	410 MHz ... 430 MHz	2400 MHz ... 2690 MHz	4900 MHz ... 7125 MHz	1559 MHz ... 1610 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	1.8	1.8	1.8
Gain	4 dBi	7 dBi	7 dBi	
Isolation between Ports	20 dB	20 dB	20 dB	
Ambient Temperature	25 °C	25 °C	25 °C	
Composite Power max	40 W	40 W	30 W	

	Band 5
Name	Socket
Frequency	
Impedance	
VSWR	
Gain	
Isolation between Ports	
Ambient Temperature	
Composite Power max	

Ports				
	Port 1	Port 2	Port 3	Port 4
Port name	Tetra (yellow)	Wifi 1 (blue)	GNSS (black)	(red)
Connector	SMA, plug (male)	SMA, plug (male)	TNC, plug (male)	TNC, jack (female)
Media type	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM
Cable length	0.23 m	0.2 m	0.26 m	0.3 m
Polarization	vertical	vertical	circular right	

SENCITY® Road

1399.99.0177

Ports				
	Port 1	Port 2	Port 3	Port 4
DC grounded	No	No	No	No

Connections				
Port number	Port 1	Port 2	Port 3	Port 4
Band 1	✓			
Band 2		✓		
Band 3		✓		
Band 4			✓	
Band 5				✓

Electrical data LNA	
LNA is connected to	Port 3
Input voltage	3 V ... 5 V
Current consumption	20 mA
Noise figure	1.6 dB
Total gain @90° elevation	30 dBic

Mechanical data	
Weight	0.41 kg
Dimensions	82 mm x 83 mm x 208 mm (Height x Width x Depth) Stick antenna max. length 0.5m
Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger. In the 790-5935 MHz band, indicated VSWR values are also valid for installations on non-metallic surfaces.


Interface and material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminium

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP68, IP69k
Flammability rating	ECE-R118
Solar radiation	DIN 75220
Standards	Automotive ISO 16750

SENCITY® Road
1399.99.0177

Environmental remarks
Environmental tests: ISO 16750:2010
Low corrosion designed acc. to MIL-F-14072D
ECE-R10
E-Mark
CE-Mark

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35199 / Date of publication: 26.03.2024 / uncontrolled copy