HiPer-D® Standard and High-Density Connectors



280-018P pin connectors with standard M24308 type mounting flange, crimp termination



HiPer-D® pin connectors feature crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D® features a rugged machined aluminum shell, waterproof sealing and optional ground springs for improved resistance to electromagnetic interference. Gold-plated size #20 contacts conform to M39029/64-369 and accept #20 to #24 AWG wire. Gold-plated size #22 contacts conform to M39029/58-360 and accept #22 to #28 AWG wire. Contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone face seal and rear grommet meet IP67 immersion requirement. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

Ordering Information										
Sample Part Number	280-018P	3525	ME	G	P					
Basic Part Number	280-018P									
Shell Size- Contact Arrangement	See Shell Size - Contact Arrangements Table			ı						
Shell Finish	ME = Electroless NickelMT =JF = Cadmium with Yellow ChromateZ2 =Z1 = Passivated Stainless Steel									
Ground Spring	G = Supplied with EMI Ground Spring N = N	No Ground Sprin	g							
Mating Hardware	L = Jackscrew, Hex Head, Low Profile K = J	P = #4-40 Female Jackpost K = Jackscrew, Slot Head, Extended Length T = Screwlock, Male, Slot Head, Extended Length					1			

Shell Size - Contact Arrangements									
Shell Size-	Shell Size- Contact Siz								
Contact Arr.	#20	#22							
Standard Density									
159	9								
2S15	15								
3\$25	25								
4S37	37								
5S50	50								
Higl	n Density								
1H15		15							
2H26		26							
3H44		44							
4H62		62							
5H78		78							
6H104		104							

Mating Hardware								
N Thru-Hole No Hardware	P Female Jackpost							
	#4-40 UNC-2A NUT AND LOCKWASHER #4-40 UNC-2B							
S Captive Screwlock, Hex Head	L Captive Jackscrew, Hex Head							
RETAINER #4-40 UNC-2A	RETAINER -#4-40 UNC-2A							
K Slot-Head Extended Jackscrew	T Slot-Head Extended Captive Screwlock							
1.1 (28) MAX MAX RETAINER -#4-40 UNC-2A	1.1 (28) MAX RETAINER -#4-40 UNC-2A							

Materials and Finishes							
Shell	Aluminum alloy						
Contacts	Copper alloy, 50 microin. gold plated						
Insulators	Thermoset epoxy						
Retention Clips	Copper alloy						
Grommet and Seal	Fluorosilicone rubber						
EMI Spring	Copper alloy, nickel plated						
Hardware	300 series stainless steel						

Specifications							
Current Rating	#22 5 AMPS, #20 7.5 AMPS						
Test Voltage	1000 VAC RMS						
Insulation Resistance	5000 megohms minimum						
Operating Temperature	-65° C. to +200° C.						
Ingress Protection	IP 67						
Shock	300 g.						
Vibration, Random	43.92 g.						


Ľ

HiPer-D® Standard and High-Density Connectors



280-018P pin connectors with standard M24308 type mounting flange, crimp termination

280-018P DIMENSIONS



	Α		В		C Basic		D		E		F Max.		G Max.	
Shell Size	in ± .015	mm ± 0.38	in ± .015	mm ± 0.38	in.	mm	in ± .005	mm ± 0.13	in ± .005	mm ± 0.13	in.	mm	in.	mm
1	1.213	30.81	.494	12.55	.984	24.99	.726	18.44	.389	9.88	.769	19.53	.432	10.97
2	1.541	39.14	.494	12.55	1.312	33.32	1.054	26.77	.389	9.88	1.093	27.76	.432	10.97
3	2.088	53.04	.494	12.55	1.852	47.04	1.594	40.49	.389	9.88	1.635	41.53	.432	10.97
4	2.729	69.32	.494	12.55	2.500	63.50	2.242	56.95	.389	9.88	2.282	57.96	.432	10.97
5	2.635	66.93	.605	15.37	2.406	61.11	2.139	54.33	.501	12.73	2.188	55.58	.544	13.82
6	2.729	69.32	.668	16.97	2.500	63.50	2.272	57.71	.563	14.30	2.312	58.72	.606	15.39

NOTES

- 1. HiPer-D® connectors are available with a wide variety of materials and finishes. See **About Series 28 HiPer-D® Shell Plating Options** for additional choices . Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
- 2. For panel cutout dimensions, refer to Panel Cutouts and Printed Circuit Board Footprints.
- 3. Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to *HiPer-D*° *Contacts and Crimp Tools* for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
- 4. HiPer-D® connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
- 5. Additional electrical, mechanical and environmental specifications are listed in HiPer-D® Product Specification.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

280-018P2S15MENN 280-018P1S9MENL 280-018P5H78MENN 280-018P1H15MENN 280-018P3H44MENL 280-018P1S9MTGN 280-018P2S15MEGN 280-018P5H78Z1GN 280-018P6H104Z1GN 280-018P3S25MENL 280-018P4S37MENL 280-018P1H15MEGL 280-018P1H15MTGS 280-046P2-3W3MTGS 280-018P2S15MEGL 280-018P1S9JFGN 280-018P2H26Z1GL 280-018P2H26Z1NL 280-018P3H44MEGP 280-018P3H44Z1GL 280-018P3S25MTNN 280-018P4H62MEGN 280-018P5S50JFNN 280-018P3S25MENN 280-018P1S9MEGN 280-018P3S25MTGP 280-018P1S9MEGN-429G 280-018P1H15MENS 280-018P1S9MEGP 280-018P2H26Z1NS 280-018P4H62MENS 280-018P5H78MENL 280-018A1S9MEGS 280-018A2H26MEGS 280-018A3H44MEGS 280-018P1H15MEGN 280-018P2H26MENN 280-018P2H26NFGN 280-018P2S15MTGT 280-018P2S15Z1GS 280-018P4H62MENN 280-018P5H78MEGN 280-018P1S9MEGL 280-018P3H44Z2NT 280-018P2H26MTGN 280-018P3H44Z2NS 280-018P6H104MEGL 280-018P5H78Z1NN 280-018P6H104MEGL-429K 280-018A1H15MTGP 280-018A2S15MEGN 280-018A3H44MEGN 280-018A3H44MTGP 280-018A3S25MEGN 280-018A4H62MEGS 280-018A5S50MEGS 280-018A6H104MTGP 280-018P1H15JFGN 280-018P1H15JFNK 280-018P1H15MEGK 280-018P1H15MEGT 280-018P1H15MENK 280-018P1H15MENN-422B 280-018P1H15MENT 280-018P1H15MTGP 280-018P1H15MTGT 280-018P1H15MTNN 280-018P1H15NFGN 280-018P1H15Z1GL 280-018P1H15Z1GT 280-018P1H15Z2GN 280-018P1S9JFNT 280-018P1S9MEGK 280-018P1S9MENK 280-018P1S9MENN-422B 280-018P1S9MENN-432 280-018P1S9MENP-432 280-018P1S9MTGP 280-018P1S9MTNN 280-018P1S9NFGL 280-018P1S9NFGN 280-018P1S9Z1GL 280-018P1S9Z1GN 280-018P1S9Z2GN 280-018P2H26JFGP 280-018P2H26JFNN 280-018P2H26JFNN-660 280-018P2H26JFNP 280-018P2H26MEGL 280-018P2H26MEGS 280-018P2H26MEGS-660-15 280-018P2H26MEGS-660-17 280-018P2H26MEGS-660-27 280-018P2H26MEGS-660-29 280-018P2H26MEGS-660-5 280-018P2H26MENL-771 280-018P2H26MENL-901 280-018P2H26MENP 280-018P2H26MENS 280-018P2H26MENT