

STAINLESS STEEL

CONNECTOR DESIGNATOR

A



ROTATABLE COUPLING

620AS001 U 16

Basic Part No. _____

Finish _____
 Z1 = Passivate
 U = Black Cadmium

Shell Size _____



See inside back cover fold-out or page 14 for Table I.

TABLE III: CABLE ENTRY

Shell Size	E Nom	F Max	Cable Entry			
			Closed		Open	
08	.555 (14.1)	.752 (19.1)	.125	(3.2)	.204	(5.2)
10	.665 (16.9)	.832 (21.1)	.187	(4.7)	.286	(7.3)
12	.790 (20.1)	.988 (25.1)	.291	(7.4)	.416	(10.6)
14	.790 (20.1)	1.046 (26.6)	.351	(8.9)	.476	(12.1)
16	.915 (23.2)	1.319 (33.5)	.501	(12.7)	.626	(15.9)
18	1.165 (29.6)	1.451 (36.9)	.518	(13.2)	.706	(17.9)
20	1.290 (32.8)	1.557 (39.5)	.581	(14.8)	.831	(21.1)
22	1.415 (35.9)	1.653 (42.0)	.644	(16.4)	.956	(24.3)
24	1.540 (39.1)	1.775 (45.1)	.706	(17.9)	1.081	(27.5)
28	1.690 (42.9)	2.020 (51.3)	.750	(19.1)	1.187	(30.1)
32	1.890 (48.0)	2.391 (60.7)	.875	(22.2)	1.250	(31.8)
36	2.270 (57.6)	2.496 (63.4)	.938	(23.8)	1.375	(34.9)

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[620AS001U10](#) [620AS001U16](#) [620AS001U20](#) [620AS001Z116](#) [620AS001Z124](#) [620AS001Z128](#) [620AS001Z132](#)
[620AS001U18](#)