



N = Number of poles
 Dim A = $N \times 5.08 + 1.0$
 Dim B = $(N - 1) \times 5.08$
 Dim C = $N \times 5.08 + 2.1$

	Dim A	Dim B	Dim C
2-6p	±0.10	±0.15	±0.15
7-12p	±0.20	±0.20	±0.20
13-16p	±0.30	±0.25	±0.25
17-24p	±0.40	±0.35	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item :Terminal housing:Thermoplastic (UL94 V-0)
- Item :Flange screw: Steel Zinc plated, M2.5, "+/-" slot type

Electrical (Match with AR series)

- Voltage rating: 300V
- Current rating: 10A
- Wire range: 1.5~2.5mm²
- Withstanding Voltage: 1.6KV

KV xx 50 x 1 xxxx G

No. OF POLES

- 02 2 CONTACTS
- 03 3 CONTACTS
-
- 24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KV 5.08 SERIES (Flange With Screw & Low profile)						
PART NO.	KVxx50x1xxxxG			DWG NO.	8KV0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Kind	Kind			Tolerance	
		2009.12.15	2009.08.10			X.	±0.50
						X.X	±0.30
						X.XX	±0.10
						X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KV0250510000G</u>	<u>KV0350510000G</u>	<u>KV0450510000G</u>	<u>KV0550510000G</u>	<u>KV0650510000G</u>	<u>KV0750510000G</u>
<u>KV0850510000G</u>	<u>KV0950510000G</u>	<u>KV1050510000G</u>	<u>KV1150510000G</u>	<u>KV1250510000G</u>	<u>KV1350510000G</u>
<u>KV1450510000G</u>	<u>KV1550510000G</u>	<u>KV1650510000G</u>	<u>KV1750510000G</u>	<u>KV1850510000G</u>	<u>KV1950510000G</u>
<u>KV2050510000G</u>	<u>KV2150510000G</u>	<u>KV2250510000G</u>	<u>KV2350510000G</u>	<u>KV2450510000G</u>	