

DO NOT SCALE  
FROM THIS PRINT.

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED

TOLERANCES ARE:

ONE PLACE DECIMALS  $\pm .1$  [.3]THREE PLACE DECIMALS  $\pm .005$  [.13]TWO PLACE DECIMALS  $\pm .01$  [.3]FOUR PLACE DECIMALS  $\pm .0020$  [.051]





ANGLES

 $\pm 2^\circ$ TITLE:  
MODIFIED LOW PROFILE  
TERMINAL ASSEMBLY

DWG NO:

MTLW-1XX-XX-XX-X-XXX-XX-XX

SHEET 1 OF 2



## NOTES:

- 1.) MAX ALLOWABLE BOW AFTER ASSEMBLY: .005 [.13] IN/IN.
- 2.) TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
- 3.) MAX PIN ROTATION IN BODY: 2°.
- 4.)  $\odot$  REPRESENTS A CRITICAL DIMENSION
- 5.) MAX CUT FLASH .010 [.25].
- 6.) GOLD CONTACT AREA LOCATION FOR G, H, S, L, & F PLATINGS.
- 7.) ORIENTATE PINS TO REDUCE THE NUMBER OF BANDOLIER MARKS IN THE POST AREA. (SEE TABLE 2)

TABLE 1

| LEAD STYLE | TERMINAL      | "L"          | "A" (FOR .090 [2.29] TAIL) | "B"         |
|------------|---------------|--------------|----------------------------|-------------|
| -05        | T-1S6-21-XX-2 | .335 [8.51]  | .185 [4.70]                | .050 [1.27] |
| -06        | T-1S6-18-XX-2 | .300 [7.62]  | .150 [3.81]                | .050 [1.27] |
| -07        | T-1S6-07-XX-2 | .430 [10.92] | .280 [7.11]                | .165 [4.19] |
| -08        | T-1S6-08-XX-2 | .530 [13.46] | .380 [9.65]                | .165 [4.19] |
| -09        | T-1S6-09-XX-2 | .730 [18.54] | .580 [14.73]               | .165 [4.19] |
| -10        | T-1S6-10-XX-2 | .830 [21.08] | .680 [17.27]               | .165 [4.19] |
| -22        | T-1S6-15-XX-2 | .630 [16.00] | .480 [12.19]               | .165 [4.19] |
| -23        | T-1S6-16-XX-2 | .445 [11.30] | .295 [7.49]                | .165 [4.19] |
| -24        | T-1S6-17-XX-2 | .480 [12.19] | .330 [8.38]                | .165 [4.19] |

CRITICAL DIMENSION INSPECTION INSTRUCTION TABLE

| ASSEMBLY OPERATION | IN-PROCESS INSPECTION |
|--------------------|-----------------------|
| FILL               | *C1, C5               |
| 2ND PRESS          | *C1                   |
| REPRESS            | *C1                   |
| CRIMP              | C4                    |
| MULTI CUT          | C2, C3                |
| * WHEREVER APPLIES |                       |

## MATERIAL:

LCP, UL 94 VO  
COLOR: BLACK

## TERMINALS:

PHOSPHOR BRONZE ALLOY  
NO. 510, 3/4 HARD  
TENSILE RANGE 95-105 KSI**santec**520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150  
PHONE (812) 944-6733 P.O. BOX 1147  
CODE 55322

MADE BY: REIDINGER 6-5-91

CHECKED BY: MCCARTIN

END

APPROVAL  
DEM

MTLW-1XX-XX-XX-X-XXX-XX-XX

SHEET 1 OF 2

## \* PROPRIETARY NOTE \*

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND IS NOT TO BE REPRODUCED, COPIED, OR DISCLOSED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF SAMTEC, INC. THE INFORMATION CONTAINED HEREIN IS THE PROPERTY OF SAMTEC, INC. AND IS NOT TO BE REPRODUCED, COPIED, OR DISCLOSED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF SAMTEC, INC.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MTLW-105-07-L-D-200](#) [MTLW-102-23-L-S-255](#) [MTLW-102-09-T-S-500](#) [MTLW-103-05-S-D-120](#) [MTLW-103-06-G-S-155](#) [MTLW-103-07-G-S-240](#) [MTLW-105-07-L-S-250](#) [MTLW-105-05-L-S-157](#) [MTLW-106-06-T-S-125](#) [MTLW-107-06-L-D-145](#) [MTLW-106-05-G-D-160](#) [MTLW-106-07-G-S-280](#) [MTLW-107-07-S-D-280](#) [MTLW-108-06-G-D-120](#) [MTLW-105-07-T-S-270](#) [MTLW-108-07-G-S-200](#) [MTLW-106-07-S-S-235](#) [MTLW-108-07-L-S-195](#) [MTLW-110-06-S-D-130](#) [MTLW-105-07-L-S-235](#) [MTLW-105-09-S-S-530](#) [MTLW-114-22-G-S-270](#) [MTLW-105-07-G-S-260](#) [MTLW-106-07-G-D-230](#) [MTLW-107-07-T-D-240](#) [MTLW-108-07-G-D-275](#) [MTLW-116-07-S-S-290](#) [MTLW-125-07-L-D-240](#) [MTLW-120-07-G-S-235](#) [MTLW-120-06-G-D-160](#) [MTLW-125-07-G-D-245](#) [MTLW-114-07-S-S-185](#) [MTLW-125-06-L-D-135](#) [MTLW-136-05-G-S-200](#) [MTLW-101-07-T-S-255](#) [MTLW-102-06-G-S-110](#) [MTLW-101-06-G-D-125](#) [MTLW-101-06-S-D-105](#) [MTLW-102-07-G-D-250](#) [MTLW-103-07-G-D-270](#) [MTLW-104-06-T-S-150](#) [MTLW-104-06-T-S-195](#) [MTLW-105-06-G-S-150](#) [MTLW-105-07-G-D-220](#) [MTLW-102-07-T-S-270](#) [MTLW-104-08-G-S-350](#) [MTLW-105-07-L-D-240](#) [MTLW-107-06-G-D-100](#) [MTLW-104-07-S-D-245](#) [MTLW-107-07-T-S-280](#) [MTLW-108-05-T-D-185](#) [MTLW-106-07-G-S-189](#) [MTLW-106-09-T-S-500](#) [MTLW-107-24-T-D-110](#) [MTLW-103-09-G-D-470](#) [MTLW-110-07-L-D-190](#) [MTLW-105-07-L-S-240](#) [MTLW-108-05-G-D-216](#) [MTLW-103-08-SM-S-280](#) [MTLW-105-24-T-D-305](#) [MTLW-109-10-T-S-380](#) [MTLW-110-09-G-D-580](#) [MTLW-132-06-S-D-130](#) [MTLW-130-08-L-D-470](#) [MTLW-112-05-G-S-175](#) [MTLW-112-08-G-S-345](#) [MTLW-125-07-G-D-280](#) [MTLW-116-05-T-S-185](#) [MTLW-136-24-T-D-330](#) [MTLW-140-10-T-S-680](#) [MTLW-102-07-T-S-319](#) [MTLW-103-05-G-S-225](#) [MTLW-104-07-G-D-255](#) [MTLW-101-05-G-S-160](#) [MTLW-102-06-G-D-170](#) [MTLW-103-06-L-S-130](#) [MTLW-103-07-G-S-150](#) [MTLW-104-07-S-D-184](#) [MTLW-101-05-G-S-185](#) [MTLW-104-08-S-D-380](#) [MTLW-102-24-T-S-280](#) [MTLW-103-05-T-S-175](#) [MTLW-103-08-T-D-373](#) [MTLW-105-23-G-D-267](#) [MTLW-105-05-L-S-160](#) [MTLW-102-09-T-D-400](#) [MTLW-104-07-S-S-275](#) [MTLW-106-07-S-D-230](#) [MTLW-107-06-T-D-120](#) [MTLW-108-22-G-S-430](#) [MTLW-105-05-G-S-185](#) [MTLW-105-08-T-D-185](#) [MTLW-106-05-T-D-170](#) [MTLW-108-07-S-D-242](#) [MTLW-110-07-L-D-270](#) [MTLW-113-06-G-D-130](#) [MTLW-108-08-G-S-230](#) [MTLW-120-07-L-D-235](#) [MTLW-113-07-S-D-230](#) [MTLW-124-07-L-S-210](#)