



FB13A Series



1. Features of FB13A Series:

- Ferrite based SMD inductor with lower core loss.
- Inductance range: 90.0 nH to 300.0 nH , custom values are welcomed.
- High current output chokes , up to 134.0 Amp with approx. 20% roll off.
- Low Profile 9.00 mm Max. height .
- 9.60 x 6.40 mm Foot Print.
- Ideal for Buck Converter, VRM & High Density Board Design.
- Operating frequency of up to 5.0MHz.
- Operating temperature range of -55° C to + 130° C. RoHS & HF compliant.
- T & R Qty's : 500pcs, 13" Reel.






2. Electrical Characteristics of FB13A Series:

ITG Part Number	OCL ¹ (nH) ± 10%	L @ Isat1 ² (nH) Min.	DCR ³ (mΩ) ± 5%	Isat1 ⁴ (A) @25°C	Isat2 ⁴ (A) @75°C	Isat3 ⁴ (A) @100°C	Isat4 ⁴ (A) @125°C	Irms ⁵ (A) @25°C
FB13A-90K	90.00	65.00	0.17	134.00	120.00	114.00	107.00	66.00
FB13A-100K	100.00	72.00	0.17	100.00	92.00	86.00	84.00	66.00
FB13A-120K	120.00	86.00	0.17	94.00	84.00	80.00	75.00	66.00
FB13A-150K	150.00	108.00	0.17	75.00	70.00	65.00	61.00	66.00
FB13A-170K	170.00	122.00	0.17	65.00	60.00	56.00	53.00	66.00
FB13A-180K	180.00	130.00	0.17	60.00	54.00	52.00	48.00	66.00
FB13A-210K	210.00	151.00	0.17	48.00	45.00	43.00	39.00	66.00
FB13A-220K	220.00	158.00	0.17	44.00	42.00	39.00	37.00	66.00
FB13A-300K	300.00	216.00	0.17	33.00	30.00	29.00	27.00	66.00

3. Mechanical Dimension of FB13A Series:

A	B	C	D	E	F
Max.	Max.	Max.	± 0.35	Nom.	± 0.20
9.60	6.40	9.00	2.60	4.00	2.60



Notes:

1. Open Circuit Inductance (OCL) test condition: 100KHz, 1.0Vrms, 0A_{dc} at 25°C.
2. L @ Isat and L @ Irms Test condition: 100KHz, 1.0Vrms (T_a=25°C).
3. The nominal DCR is measured from point "a" and "a" to point "b" and "b", as shown above on the mechanical drawing (T_a=25°C).
4. Isat1 , Isat2 , Isat3 & Isat4 : DC current that will cause inductance to drop approximately by 20%.
5. Irms : DC current for an approximate temperature rise of 40°C without core loss. Derating is necessary for AC currents. PCB pad layout, trace thickness and width ,air -flow and proximity of other heat generating components will affect the temperature rise.
6. It is recommended the part temperature not exceed 130° C under worst case operating conditions as verified in the end application.

● New York 1 914 347 2474 ● Taipei 886 2 2698 8669 ● Kaohsiung 886 7 350 2275
 ● Japan 81 568 85 2830 ● Shenzhen 86 755 8418 6263 ● Shanghai 86 21 5424 5141 ● Hong Kong 852 9688 9767
 ● sales@ITG-Electronics.com ● www.ITG-Electronics.com Revision B.1: April 26 , 2018





**Due to continuous product improvement, all specifications are subject to change without prior notice. Kindly contact an ITG field application engineer or a sales representative prior to purchase.*



FB13A Series



4. Inductance Characteristics of FB13A Series (Inductance vs Current):







● New York 1 914 347 2474 ● Taipei 886 2 2698 8669 ● Kaohsiung 886 7 350 2275
 ● Japan 81 568 85 2830 ● Shenzhen 86 755 8418 6263 ● Shanghai 86 21 5424 5141 ● Hong Kong 852 9688 9767
 ● sales@ITG-Electronics.com ● www.ITG-Electronics.com Revision B.1: April 26, 2018

**Due to continuous product improvement, all specifications are subject to change without prior notice. Kindly contact an ITG field application engineer or a sales representative prior to purchase.*



FB13A Series




● New York 1 914 347 2474 ● Taipei 886 2 2698 8669 ● Kaohsiung 886 7 350 2275
 ● Japan 81 568 85 2830 ● Shenzhen 86 755 8418 6263 ● Shanghai 86 21 5424 5141 ● Hong Kong 852 9688 9767
 ● sales@ITG-Electronics.com ● www.ITG-Electronics.com Revision B.1: April 26, 2018

**Due to continuous product improvement, all specifications are subject to change without prior notice. Kindly contact an ITG field application engineer or a sales representative prior to purchase.*



FB13A Series



● New York 1 914 347 2474 ● Taipei 886 2 2698 8669 ● Kaohsiung 886 7 350 2275
● Japan 81 568 85 2830 ● Shenzhen 86 755 8418 6263 ● Shanghai 86 21 5424 5141 ● Hong Kong 852 9688 9767
● sales@ITG-Electronics.com ● www.ITG-Electronics.com Revision B.1: April 26 , 2018

**Due to continuous product improvement, all specifications are subject to change without prior notice. Kindly contact an ITG field application engineer or a sales representative prior to purchase.*