








PCB hole pattern, mounting side



4	2	Snap-in bolt	PCB 1.6mm / Brass	tin plated
3	41	Signal contact	P1 / Brass	0.8µm Au
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green
<i>No.</i>	<i>St.</i>	<i>Part</i>	<i>Type Description/Material</i>	<i>Surface plating/Colour/Class</i>

FUNCTIONAL SYMBOLS  = 0  = 0  = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS mm		SCALE 2:1		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m				molex						
					CURRENT REVISION				FCT D-Sub Mixed-Layout Connector						
				DRWN: DRAWN BY msteinbrueck 26-04-2023											
				APPR: APPR BY fvetter 27-04-2023											
	2		24130		INITIAL REVISION				PRODUCT CUSTOMER DRAWING						
	1				DRWN: DRAWN BY Denzinger 15-09-2003				MATERIAL NUMBER				REVISION		
	REV.		CH.-NO.		APPR: APPR BY aschiekofer 16-09-2003				1731071794				2		
REPLACEMENT FOR:				FRIST ANGLE PROJECTION 		DRAWING A3-SIZE		DOCUMENT NUMBER FM43W2P1-0982				CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1	

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.