

IEC Appliance Inlet C8, insert Mounting, Solder, PCB or Quick-connect Terminal



C8

 70 °C

**Description**

Drop-in type Appliance Inlet,
 - Pin temperature 70 °C, Protection class II

Approvals

- VDE Certificate Number: 40002274
 - UL File Number: E96454
 - CSA File Number: 27324

References

We recommend for new applications the type [0720-FP](#)


Weblinks

[pdf](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#), [Wire Harness](#)

Technical Data

Ratings IEC	2.5 A / 250 VAC; 50 Hz
Ratings UL/CSA	2.5 A / 250 VAC; 60 Hz
Dielectric Strength	> 4 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class 2 acc. to IEC 61140
Terminal	straight
Material: Housing	PA6, black / grey / white, UL 94V-0

Appliance Inlet	C8 acc. to IEC/EN 60320-1 UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 2.5 A, Protection Class 2
-----------------	--

Dimensions

Length of the terminal please find at the order code configuration table

Config. Code

2572 - H - A B C 0- D - E G F

The characters are placeholders for the correspondingly keys of selections from the key tables.

2572 - H - A B C 0- D - E G F = Type

Type	Configuration key
protection class 2	B

2572 - H - A B C 0- D - E G F = Terminals

Terminal L	Configuration key
short solder terminal (L = 4.8 mm)	2
long solder terminal (L = 8.5 mm)	3
PCB-terminal (standard)	4
PCB-terminal (short)	5
PCB-terminal (long)	6
Blade terminal (2.8 x 0.8 mm)	7
Blade terminal (4.8 x 0.8 mm)	8

2572 - H - A B C 0- D - E G F = Terminals

Terminal N	Configuration key
short solder terminal (L = 4.8 mm)	2
long solder terminal (L = 8.5 mm)	3
PCB-terminal (standard)	4
PCB-terminal (short)	5
PCB-terminal (long)	6
Blade terminal (2.8 x 0.8 mm)	7
Blade terminal (4.8 x 0.8 mm)	8

Symbols similar as in table A

2572 - H - A B C 0- D - E G F = Terminals

Terminal Ground	Configuration key
without terminal	0

Symbols similar as in table A

2572 - H - A B C 0- D - E G F = Color

Color	Configuration key
jet black; RAL9005	A
silver grey; RAL7001	B
pure white; RAL9010	D

2572 - H - A B C 0- D - E G F = Style

Style	Configuration key
insert type	5

2572 - H - A B C 0- D - E G F = Dimension X

Dimension "X"	Configuration key
00	

The dimension "X" is displayed in ($\frac{1}{10}$ mm). This information is also valid for the order code

2572 - H - A B C 0- D - E G F = Orientation of Terminals

Orientation of Terminals	Configuration key
horizontal	A
vertical	B

Variants


Config. Code	Description	Order Number
2572--2200-A-500A	2572, IEC Appliance Inlet C8, 70°C, version: 2, L: short solder terminal (L=4,8mm), N: short solder terminal (L=4,8mm), ground: without terminal, color: jet black; RAL9005, design: insert type	6160.0008
2572--5500-A-500A	2572, IEC Appliance Inlet C8, 70°C, version: 2, L: PCB-terminal (short), N: PCB-terminal (short), ground: without terminal, color: jet black; RAL9005, design: insert type	6160.0009
2572--6600-A-500A	2572, IEC Appliance Inlet C8, 70°C, version: 2, L: PCB-terminal (long), N: PCB-terminal (long), ground: without terminal, color: jet black; RAL9005, design: insert type	6160.0010
2572--7700-A-500B	2572, IEC Appliance Inlet C8, 70°C, version: 2, L: Blade terminal (2.8 x 0.8 mm), N: Blade terminal (2.8 x 0.8 mm), ground: without terminal, color: jet black; RAL9005, design: insert type	6160.0011
2572--8800-A-500B	2572, IEC Appliance Inlet C8, 70°C, version: 2, L: blade terminal (4,8x0,8mm), N: blade terminal (4,8x0,8mm), ground: without terminal, color: jet black; RAL9005, design: insert type	6160.0026

The listed variants should be available from stock. Other versions on request www.schurter.com/contact

Packaging unit 100 Pcs

Accessories

Description



[Assorted Covers](#)
Rear Cover



[Wire Harness](#)
Wire harness for SCHURTER products

Mating Outlets/Connectors

Category / Description

[Power Cord](#)[Overview complete](#)



Power Cord with IEC Connector C7, Straight 70°C	2510
Power Cord with IEC Connector C7, Angled	2511
Power Cord with IEC Plug C7, Angled	2514
Power Cord with IEC Connector C7, Straight 70°C	4810

[Power Cord](#)[further types to2572](#)