

COAXIAL CONNECTOR, BNC, 75 Ohm, Straight bulkhead cable jack (female)

24_BNC-75-3-5/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration

Gender	Standard
jack	Interface compatible with IEC 61169-8

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper Beryllium Alloy	SUCOPLATE (R) Plating

Electrical data

Impedance	75 Ω
Interface frequency	1 GHz

Mechanical data

Weight	0.0161 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data

Operation temperature	-65 °C ... 165°C
-----------------------	------------------

Suitable cables

Cable group	U14 - 3 mm / 75 Ohm
Suitable cables	G_03233_D

COAXIAL CONNECTOR, BNC, 75 Ohm, Straight bulkhead cable jack (female)
24_BNC-75-3-5/133_N**Additional Information**

Only as assembly	No
------------------	----

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2654 / Date of publication: 25.11.2023 / uncontrolled copy