

## Product Overview

### XGS 5000: CMOS Image Sensor, 5.3 MP, Global Shutter

For complete documentation, see the data sheet.

#### Information

The XGS 5000 is a 5.3 Mp (2592 x 2048) CMOS image sensor in 2/3 inch optical format, supporting up to 132 frames per second readout with 12-bit output at full resolution.

The device provides high resolution, global shutter imaging with high readout speed for industrial imaging customers. A compact package design and low power footprint make the device compatible with a 29 x 29 mm<sup>2</sup> camera footprint. Two speed grades are available to match device output to key computer interfaces and application requirements.

The XGS 5000 shares a common design and footprint with other members of the XGS family, allowing one camera design to support multiple resolutions to simplify and speed time to market for new camera designs.

The XGS 5000 is available in a 163-pin iLGA package in both monochrome and Bayer color configurations.

#### Features

- Advanced 3.2 µm global shutter pixel
- Energy efficient design
- Compact package
- Available speed grades

#### Applications

- Image Capture

#### Benefits

- High resolution with high image quality and uniformity
- Reduced power and thermal footprints
- Compatible with 29 x 29 mm<sup>2</sup> camera design
- Match to key computer interfaces and application requirements

#### End Products

- Industrial cameras and systems
- Inspection system (food, bottles, recycling labels, etc.)
- Intelligent Transportation Systems (ITS)
- Security cameras and systems
- Machine Vision camera

#### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Package Type
NOIX4SE5000B-LTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	5.3	132	2/3 inch	Global Shutter	3.2 x 3.2	HiSPi™	Bayer Color	ILGA163 16x16
NOIX4SF5000B-LTI		Pb-free Halide free non AEC-Q and PPAP	Active									ILGA163 16x16
NOIX4SN5000B-LTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	5.3	132	2/3 inch	Global Shutter	3.2 x 3.2	HiSPi™	Mono	ILGA163 16x16
NOIX5SE5000B-LTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	5.3	43	2/3 inch	Global Shutter	3.2 x 3.2	HiSPi™	Bayer Color	ILGA163 16x16
NOIX5SN5000B-LTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	5.3	43	2/3 inch	Global Shutter	3.2 x 3.2	HiSPi™	Mono	ILGA163 16x16

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 11/22/2021