

LZ0E01PS

('ON 0NIMVHD)各要図





TABLE 1

PART NUMBER	DIMENSION IN MILLIMETERS								NUMBER OF CONTACTS コネクタ本数		
	±0.5 A	±0.13 B	±0.25 C	±0.25 C'	±0.25 D	±0.25 E	±0.25 E'	±0.25 F	#1	#2	#3
DE-9PA-NR	31.1	24.99	—	16.90	12.6	—	8.34	8.64	4	5	—
DE-9SA-NR	31.1	24.99	16.26	—	12.6	7.82	—	8.64	4	5	—
DA-15PA-NR	39.4	33.32	—	25.24	12.6	—	8.34	8.64	7	8	—
DA-15SA-NR	39.4	33.32	24.59	—	12.6	7.82	—	8.64	7	8	—
DB-25PA-NR	53.1	47.04	—	39.01	12.6	—	8.40	8.64	12	13	—
DB-25SA-NR	53.1	47.04	38.30	—	12.6	7.82	—	8.64	12	13	—
DC-37PA-NR	69.6	63.50	—	55.47	12.6	—	8.40	8.64	18	19	—
DC-37SA-NR	69.6	63.50	54.76	—	12.6	7.82	—	8.64	18	19	—
DD-50PA-NR	67.2	61.11	—	52.86	15.4	—	11.16	10.03	17	16	17
DD-50SA-NR	67.2	61.11	55.47	—	15.4	10.65	—	10.03	17	16	17

NOTE1. MARK THE COMPANY NAME AND ABBREVIATED PART NUMBER AT THE LOCATION SHOWN IN THE DRAWING.

2.FOR APPLICABLE P.C.B. DIMENSION,SEE DWG.NO.SJ014290.

3.THIS DRAWING SHOWS NUMBER OF CONTACTS 25.
FOR CONTACT ARRANGEMENT,SEE DWG.NO.SJ010210.

△ 4.LOT NUMBER AT THE LOCATION SHOWN IN THE DRAWING.
MARKING LOCATION IS SHOWN ON THE FRONT SHELL FACE
FOR SOCKET SIDE,ON THE REAR SHELL FACE FOR PIN SIDE.

注1. 図示の位置に社名及び、品名略称を表示する。

2. 本製品の基板取付寸法SJ014290を参照のこと。

3. 本図のコンタクト配列は、25芯の場合を示す。
その他の配列についてはSJ010210を参照のこと。

△ 4. 図示の位置にロット番号を表示する。
表示位置はソケット側がフロントシェル面、ピン側はリアシェル面に表示されている。

DESIGNATION

命名法

SERIES
シリーズ
SHELL SIZE
シェルサイズ

D※-※A-NR

MODIFICATION CODE

特殊記号

CONTACT TYPE(S:SOCKET,P:PIN)


コンタクト区分

CONTACT ARRANGEMENT

コンタクト配列


VIEW OF DA,DB,DC,DE SIZES

DA、DB、DC、DEの場合




VIEW OF DD SIZE

DDの場合



9	PAN HEAD MACHINE SCREW	2	STEEL	HEXAVALENT CHROMIUM FREE CHROMATE (TRIVALENT CHROMATE TREATMENT) ON ELECTROPLATED ZINC	M2.6
8	SPRING WASHER	2	STEEL	HEXAVALENT CHROMIUM FREE CHROMATE (TRIVALENT CHROMATE TREATMENT) ON ELECTROPLATED ZINC	M2.6
7	HEXAGON NUT	2	COPPER ALLOY	HEXAVALENT CHROMIUM FREE CHROMATE (TRIVALENT CHROMATE TREATMENT) ON ELECTROPLATED ZINC	M2.6
6	CONTACT #3	TABLE1	COPPER ALLOY	GOLD OVER NICKEL PLATING	
5	CONTACT #2	TABLE1	COPPER ALLOY	GOLD OVER NICKEL PLATING	
4	CONTACT #1	TABLE1	COPPER ALLOY	GOLD OVER NICKEL PLATING	
3	BRACKET	1	GLASS FILLED PBT	(COLOR: BLACK)	UL94V-0
2	SHELL	2	STEEL	HEXAVALENT CHROMIUM FREE CHROMATE (TRIVALENT CHROMATE TREATMENT) ON ELECTROPLATED ZINC	
1	INSULATOR	2	GLASS FILLED PBT	(COLOR: BLACK)	UL94V-0
符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS

仕様書 (SPECIFICATION) JACS-1045-5		第1版 (ORIGINAL DATE) 31.Mar.2005		尺度 (SCALE) 2: 1	シリーズ (SERIES) Dsub	日本航空電子工業株式会社 JAE ELECTRONICS INDUSTRY, LTD. 図面番号 (DRAWING NO.) SJ103071
一般公差 (GENERAL TOLERANCE)		製図 DR.		名称 (TITLE) D※-※A-NR		
寸法 (DIMENSION)	角度 (ANGLES)	担当 CHK.	Y.TAKAGI			
		査閲 APPD.				
		承認 APPD.	Y.KUBOTA			
. ±	×° ±			質量 (MASS)		
. × ±	×°×' ±					
. ×× ±						
. ××× ±						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[DB-25SA-NR](#) [DC-37PA-NR](#) [DD-50PA-NR](#) [DE-9SA-NR](#) [DD-50SA-NR](#) [DB-25PA-NR](#)