


REVISION Q

DO NOT
SCALE FROM
THIS PRINT



HTSS-1XX-XX-XX-D-XX-XX

No OF POSITIONS

-02 (STRAIGHT ONLY)
-03 THRU -18, -20, -24,
-25, -28, -30, -32 & -36

— POLARIZATION OPTION

-XX: INDICATES POSITION OMITTED

– OPTION

BLANK: STRAIGHT (STYLES -04 & -05 N/A)
 -RA: RIGHT ANGLE (STYLES -01, -02 & -03 N/A)
 -LL: LOCKING LEAD (STRAIGHT ONLY)
 -LA: -RA OPTION WITH -LL OPTION
 (SEE TUBE TABLE FOR PACKAGING)

- ROW SPECIFICATION



-D: DOUBLE ROW
(USE HTSS-XX-D)

PLATING SPECIFICATION



-G: GOLD, 10 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
-T: MATTE TIN CONTACT AND TAIL
-S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-H: HEAVY GOLD, 30 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
-F: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-TM: MATTE TIN CONTACT AND TAIL
-SM: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-LM: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-SS: STRIPE SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
(SEE NOTE 7)

FIG 1

HTSS-111-01-XX-D-LL SHOWN



SECTION "A"-"A"



DETAIL 'B'
SCALE 6 : 1

* DIMENSIONS APPLY WHEN USING -LL OPTION ONLY

NOTES:

1.  REPRESENTS A CRITICAL DIMENSION.
2. TERMINAL PUSHOUT FORCE: 3 lbs.
3. ASSEMBLE GOLD PLATED END AS SHOWN.
4. TERMINALS TO BE FLUSH TO .010[.25] BELOW TOP OF SHROUD.
5. HTSS-1XX-04-XX-D-XA-XX ASSEMBLIES ARE TO BE PACKAGED IN A PT-1-24-01-40 TUBE WITH TWO TP-13 PLUGS PER TUBE (ALL POSITIONS).
6. SAMTEC LOGO MAY VARY IN LOCATION.
7. AVAILABLE ON STRAIGHT LEAD STYLES -01, -02, -03 AND ON -RA LEAD STYLE -04. MATES ONLY WITH SSW, SSQ, SSM, BCS, ESQ.

LEAD STYLE	"A"	TERMINAL
-01	.480[12.19]	T-1S6-17-XX-2
-02	.530[13.46]	T-1S6-08-XX-2
-03	.930[23.62]	T-1S6-11-XX-2

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS	ANGLES
----------	--------

XX: +.01 [.3]

$$.XXX: \pm .005 [.13]$$
.XXX: $\pm .0020$ [.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING

INSULATOR: LCP, UL 94 VO

COLOR: NATURAL
TERMINAL: PHOS BRONZE

SHEET SCALE: 1.5:1

DESCRIPTION:

HIGH TEMP TOP SHROUD TERMINAL STRIP

DWG NO.	
---------	--

HTSS-1XX-XX-XX-D-XX-XX

BY: BRATCHER 01/20/04

SHEET 1 OF 2

F:\DWG\MISC\MKTG\HTSS-1XX-XX-XX-D-XX-XX-MKT.SLDDRW







FIG 2
-RA & -LA OPTIONS
(HTSS-111-04-XX-D-LA SHOWN)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)




.035±.010 [0.89±0.25] (TYP)


⊕*.0080 [0.20] (TYP)



* DIMENSIONS APPLY WHEN USING -LA OPTION ONLY



IN-PROCESS 1




IN-PROCESS 2


TUBE: PT-1-24-02-112
PLUG: TP-28

TUBE: PT-1-24-01-91
PLUG: TP-28


TUBE: PT-1-24-01-40
PLUG: TP-13



FOR -05(3-4) POS



FOR -05(5-36) POS



FOR -04

PACKAGING VIEW FOR LEAD STYLES -04 & -05

Packaging Table			
Lead Style	Packaging	TUBE	PLUG
-01	Bulk	N/A	N/A
-02	Bulk	N/A	N/A
-03	Bulk	N/A	N/A
-04	Tube	PT-1-24-01-40	TP-13
-05	Tube(3-4POS)	PT-1-24-02-112	TP-28
	Tube(5-36POS)	PT-1-24-01-91	TP-28

TABLE 2					
LEAD STYLE	"B"	"C"	"D"	TERMINAL #1	TERMINAL #2
-04	.130 [3.30]	.280 [7.11]	.830 [21.08]	T-1S6-15-XX-2	T-1S6-10-XX-2
-05	.230 [5.84]	.380 [9.65]	.930 [23.62]	T-1S6-09-XX-2	T-1S6-11-XX-2

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
HIGH TEMP TOP SHROUD TERMINAL STRIP

DWG. NO.
HTSS-1XX-XX-XX-D-XX-XX

BY: BRATCHER 01/20/04 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HTSS-114-04-L-D-RA](#) [HTSS-118-04-L-D-RA](#) [HTSS-120-05-H-D-LA](#) [HTSS-112-05-G-D-RA](#) [HTSS-103-01-S-D](#)
[HTSS-118-01-H-D](#) [HTSS-106-01-S-D](#) [HTSS-109-04-L-D-RA](#) [HTSS-109-01-L-D](#) [HTSS-120-04-L-D-LA](#) [HTSS-110-05-](#)
[S-D-RA](#) [HTSS-111-01-L-D](#) [HTSS-136-04-G-D-RA](#) [HTSS-103-04-L-D-RA](#) [HTSS-120-04-S-D-LA](#) [HTSS-105-02-L-D-01](#)
[HTSS-102-01-F-D](#) [HTSS-116-02-L-D](#) [HTSS-105-01-G-D-10](#) [HTSS-130-03-G-D](#) [HTSS-108-01-F-D-01](#)