




(2,00 mm) .0787"

**SQT SERIES**

COST-EFFECTIVE RUGGED SOCKETS

SPECIFICATIONS

For complete specifications see www.samtec.com?SQT

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over 50µ" (1,27 µm) Ni

Current Rating (TMMH/SQT):

5.1 A per pin
(1 pin powered per row)

Voltage Rating:

450 VAC mated with
TMM or TMMH

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

10 mΩ

Insertion Depth:

(2,62 mm) .103" to

(5,03 mm) .198"

Insertion Force:

(Single contact only)

4 oz (1,11 N) average

Normal Force:

60 grams (0,59 N) average

Withdrawal Force:

(Single contact only)

3 oz (0,83 N) average

Max Cycles:


100 with 10µ" (0,25 µm) Au

RoHS Compliant: Yes

Lead-Free Solderable: Yes

Mates with:

TMMH, TMM, MTMM,
MMT, TW, LTMM, ZLTMM,
ESQT, TCMD, PTT, TSH



Choice of one
through six rows

Vertical and
Right Angle

(2,00 mm)
.0787" pitch

(6,35 mm)
.250"



Note: Some lengths, styles
and options are non-standard,
non-returnable.

RECOGNITIONS


For complete scope
of recognitions see
www.samtec.com/quality



Other Solutions


Elevated

See ESQT Series.




Surface Mount

See SQW and
TLE Series.




Low Profile

See CLT Series.



High Reliability

See SMM Series.



Press Fit

See PTF Series.



SQT	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 50			Specify LEAD STYLE from chart	<p>-F = Gold flash on contact, Matte Tin on tail</p> <p>-L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail</p>	<p>-S = Single Row</p> <p>-D = Double Row</p> <p>-T = Triple Row</p> <p>-Q = Four Row</p> <p>-5 = Five Row</p> <p>-6 = Six Row</p>	<p>-RA = Right Angle (-Q, -5 & -6 Row not available) (Lead Style -01 only)</p> <p>-“XXX” = Polarized Position (Indicate position number)</p>

LEAD STYLE	A
-01	(2,29) .090
-02	(15,24) .600
-03	(5,28) .208

No. of positions x (2,00) .0787 + (0,30) .012

(0,38) .015

(0,51) .020 SQ

(6,35) .250

(2,00) .0787 TYP

(1,27) .050

(2,29) .090

(2,00) .0787

-RA OPTION
(-Q, -5 & -6 not available)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SQT-124-03-F-5](#) [SQT-109-01-F-5](#) [SQT-119-03-F-5](#) [SQT-117-03-F-5](#) [SQT-131-03-L-D](#) [SQT-140-02-F-T](#) [SQT-115-01-F-6](#) [SQT-109-01-F-Q](#) [SQT-133-01-L-T](#) [SQT-133-03-F-T](#) [SQT-117-03-F-Q](#) [SQT-117-02-F-5](#) [SQT-116-02-F-5](#) [SQT-141-02-F-6](#) [SQT-107-02-F-5](#) [SQT-112-02-F-Q](#) [SQT-145-01-L-T](#) [SQT-116-02-F-Q](#) [SQT-141-03-F-6](#) [SQT-144-01-F-D](#) [SQT-104-03-F-6](#) [SQT-120-01-F-6](#) [SQT-123-01-F-Q](#) [SQT-142-01-L-Q](#) [SQT-120-02-F-5](#) [SQT-144-01-L-T](#) [SQT-103-02-F-T](#) [SQT-124-01-F-T](#) [SQT-105-01-F-5](#)