

COAXIAL ADAPTER, PC 3.5 - N, 50 Ohm, plug / jack (male / female)

33_PC35-N-50-1/1--_U

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
PC 3.5	plug (male)	IEC 60169-23
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/402_CECC 22210

Interface and material data		
PC 3.5		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Bronze	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
N-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 12.4 GHz	26 dB	1.1

COAXIAL ADAPTER, PC 3.5 - N, 50 Ohm, plug / jack (male / female)
33_PC35-N-50-1/1--_U

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
12.4 GHz ... 18 GHz	23 dB	1.15
Mechanical data		
Weight	0.0428 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-55 °C ... 70 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22643958	33_PC35-N-50-1/1--_UE	Single
Additional Information		
Remarks	Operating specification acc. IEEE Std 287: temperature 13 °C to 33 °C	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2178 / Date of publication: 27.05.2024 / uncontrolled copy