


SIGN	DATE	DESCRIPTION	APPROVER
△	10/27'09	Dim.A and Dim.B tolerance table changed.	Kind
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material:

- Item a :Terminal housing:Thermoplastic (UL94 V-0)

Electrical (Match with A0 series)




- Voltage rating: 300V
- Current rating: 10A
- Wire range: 0.5-1.0mm²/1.5-2.5mm²
- Withstanding Voltage: 1.6KV

KI xx 50 x 0 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
... ...
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.



N = Number of poles
Dim A=Nx5.08
Dim B=(N-1)x5.08

Dim. Poles	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.25	±0.25
13-16p	±0.30	±0.30
17-24p	±0.40	±0.35

ANYTEK				CUSTOMER COPY					
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD									
TITLE		KI 5.08 SERIES (W/o flange)							
PART NO.		KIxx50x0xxxxG			DWG NO.		8KI0101		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
			Jacke	Jacke			UNIT: mm	X.	±0.50
			2010.03.31	2010.03.31			SCALE: 2/1	X.X	±0.30
							SHEET: 01/01	REV.: D	X.XX
							X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KI0250500000G</u>	<u>KI0350500000G</u>	<u>KI0450500000G</u>	<u>KI0550500000G</u>	<u>KI0650500000G</u>	<u>KI0750500000G</u>
<u>KI0850500000G</u>	<u>KI0950500000G</u>	<u>KI1050500000G</u>	<u>KI1150500000G</u>	<u>KI1250500000G</u>	<u>KI1350500000G</u>
<u>KI1450500000G</u>	<u>KI1550500000G</u>	<u>KI1650500000G</u>	<u>KI1750500000G</u>	<u>KI1850500000G</u>	<u>KI1950500000G</u>
<u>KI2050500000G</u>	<u>KI2150500000G</u>	<u>KI2250500000G</u>	<u>KI2350500000G</u>	<u>KI2450500000G</u>	<u>KI0550900000G</u>
<u>KI0250900000G</u>					