

# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact insert, shell size 2, with 15 signal contacts, type of contact pin, with solder cup, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-15-...



## Your advantages

- D-SUB 15 connection
- Easy assembly
- Compatible with IP67 sleeve housing and panel-mount frame

## Commercial data

Item number	1688874
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB19
Product key	ABNCAA
Catalog page	Page 210 (C-2-2013)
GTIN	4017918823023
Weight per piece (including packing)	12.99 g
Weight per piece (excluding packing)	7.43 g
Customs tariff number	85366990
Country of origin	DE

# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

## Technical data

### Product properties

Product type	Male insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Type	Male
Shielded	no

### Data management status

Article revision	02
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

### Connection data

Connection method	Solder cup
-------------------	------------

### Dimensions

Width	14.4 mm
Height	39.5 mm
Length	12.9 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel
Contact carrier material	PBT-GF

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 50
Insertion force per signal contact	≤ 3.40 N

# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C

## Mounting

Mounting type	Hole
---------------	------

# VS-15-ST-DSUB-EG - Contact insert


1688874

<https://www.phoenixcontact.com/us/products/1688874>



## Drawings

Schematic diagram



# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688874>



**UL Recognized**

Approval ID: E118976

# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

## Classifications

### ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440223
ECLASS-13.0	27440223

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-15-ST-DSUB-EG - Contact insert



1688874

<https://www.phoenixcontact.com/us/products/1688874>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c30472e6-5c56-46a0-a450-62f6874c6344

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)