

# Series 805 Mighty Mouse Triple-Start Protective Cover

667-261 and 667-262 Ordering Information



Accessories



Plug Cover



Receptacle Cover

## Protect Connectors From Damage

Machined aluminum or stainless steel protective covers have fluorosilicone gasket for a watertight fit.

## Stainless Steel Fittings and Rings

Choose small diameter eye fittings for panel attachment. Larger rings fit under the jam nut or over cable jackets. Split rings can be installed on fully assembled cables.

## Polyurethane-Coated SST Wire Rope

provide resistance and good flexibility. Or, choose a Teflon® jacket for high temperature exposure.

## Braided Nylon Rope

provides excellent flexibility and good abrasion resistance, and can be ordered with slip knot fittings for easy installation on any size cable.

How To Order						
Sample Part Number	667-262	-M	-G	9	04	-6
Series (See Table I)	<b>667-261</b> = Plug Cover <b>667-262</b> = Receptacle Cover					
Shell Material / Finish	<b>C</b> = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant <b>M</b> = Aluminum / Electroless Nickel RoHS Compliant <b>NF</b> = Aluminum / Cadmium with Olive Drab Chromate <b>ZNU</b> = Aluminum / Zinc-Nickel with Black Chromate <b>MT</b> = Aluminum / Nickel-PTFE RoHS Compliant <b>Z1</b> = Stainless Steel / Passivated RoHS Compliant					
Attachment Type	<b>D</b> = Bead Chain, CRES, Passivate <b>F</b> = Wire Rope, Nylon Jacket <b>G</b> = Nylon Rope <b>H</b> = SST Wire Rope, Teflon® Jacket <b>N</b> = No Attachment <b>R</b> = Wire Rope, PVC Jacket <b>S</b> = SST Sash Chain <b>SK</b> = Nylon Rope With Slip Knot <b>T</b> = SST Wire Rope, No Jacket <b>U</b> = SST Wire Rope, Polyurethane Jacket  "SST" = Stainless Steel					
Shell Size	<b>8, 9, 10, 11, 12, 13, 15, 18, 19, 21, 23</b>					
Attachment Code (See Table II)	Small Ring = <b>01</b> thru <b>06</b> Large Ring = <b>14</b> thru <b>33</b> Split Ring = <b>50</b> thru <b>68</b>					
Attachment Length (inches)	Omit for attachment Type N (No Attachment) Example "-6" equals six inch length					

Table I: Cover Style

<b>667-261</b> Plug Cover	<b>667-262</b> Receptacle Cover

Table II: Attachment Code

Omit for attachment types <b>N</b> (No Attachment) and <b>SK</b> (Slip Knot)	
	<b>01</b> - .126 (3.20) I.D. <b>02</b> - .145 (3.68) I.D. <b>04</b> - .188 (4.78) I.D. <b>06</b> - .197 (5.00) I.D.
	<b>14</b> - .385 (9.78) I.D. <b>15</b> - .445 (11.30) I.D. <b>33</b> - .510 (12.95) I.D. <b>16</b> - .570 (14.48) I.D. <b>17</b> - .635 (16.13) I.D. <b>18</b> - .695 (17.65) I.D. <b>27</b> - .766 (19.46) I.D. <b>31</b> - .820 (20.83) I.D. <b>19</b> - .885 (22.48) I.D. <b>26</b> - .950 (24.13) I.D. <b>27</b> - .766 (4.13) I.D. <b>28</b> - 1.015 (25.78) I.D. <b>20</b> - 1.070 (27.17) I.D. <b>22</b> - 1.210 (30.73) I.D. <b>23</b> - 1.275 (32.39) I.D. <b>30</b> - 1.380 (35.05) I.D. <b>25</b> - 1.530 (38.86) I.D. <b>26</b> - 1.530 (38.86) I.D. <b>31</b> - .820 (20.83) I.D.
	<b>50</b> - .420 (10.67) I.D. <b>52</b> - .480 (12.19) I.D. <b>54</b> - .635 (16.13) I.D. <b>56</b> - .745 (18.92) I.D. <b>58</b> - .885 (22.48) I.D. <b>60</b> - 1.010 (25.65) I.D. <b>64</b> - 1.125 (28.58) I.D. <b>68</b> - 1.345 (34.16) I.D.

Dimensions in Inches (millimeters) are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[667-262-Z1-N8](#) [667-262-NF-SK11-6](#) [667-262-NF-N11](#) [667-262-NF-N12](#) [667-261-NF-SK11-6](#) [667-261-NF-SK18-6](#)  
[667-262-Z1-N12](#) [667-262-Z1-N15](#)