






#### NOTES:

##### 备注

1.Copper,nickel base,matte tin

黄铜, 镍底, 镀雾锡

2.Wire screw hole M4

压线螺孔M4

3.Current Rating: 45A

额定电流:45A

4.There shall be no defects such as pin deformation and burrs.


不得有脚变形, 毛刺等缺陷

5.Unmarked dimensions refer to tolerances

未标注的尺寸参考公差

#### Ordering Information

| Type                  | Screw Thread | Welding Feet     | Series           | D=DIP       | Product No. | Material           |
|-----------------------|--------------|------------------|------------------|-------------|-------------|--------------------|
| M=Pull Teeth (插牙)     | 3=M4 (螺牙)    | 101=101.4mm (焊脚) | 08/8=8x8mm (系列)  | S=SMT       | 产品序号        | 默认=Copper (黄铜)     |
| RN=Rivet Nut (铆螺母)    | 4=M4 (螺牙)    | 2=2个             | 101=101.4mm (系列) | FD=Flag Dip |             | RC=Red Copper (紫铜) |
| RC=Rivet Casker (铆垫片) | 5=M5 (螺牙)    | 4=4个             |                  |             |             |                    |
|                       | 6=M6 (螺牙)    | 6=6个             |                  |             |             |                    |
|                       |              | 8=8个             |                  |             |             |                    |

| GENERAL TOLERANCE |                        |                   | 制图<br>DRAWING    | 01                                                                                    |  深圳讯答科技有限公司<br>ShenzhenXunDaTechnology Co.,Ltd |                                    |             |
|-------------------|------------------------|-------------------|------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|-------------|
| DIM TOL           |                        |                   | 审核<br>CHECK      |                                                                                       |                                                                                                                                     |                                    |             |
| X.X ±0.30         |                        |                   | 批准<br>APPROVAL   |                                                                                       | 产品名称<br>TITLE                                                                                                                       | PCB 焊接端子 (插板 铆垫片 M4 4焊脚 8x8x8.7mm) | 版本<br>REV.  |
| X.XX ±0.20        |                        |                   | 比例<br>SCALE      |                                                                                       | 产品料号<br>PART NO.                                                                                                                    | XD-RG44-0808-D001RC                | 单位<br>UNITS |
| X.XXX ±0.10       |                        |                   | 投影<br>Projection |  | 材料<br>MATERIAL                                                                                                                      |                                    | 页次<br>SHEET |
| Angle ±3.0°       |                        |                   |                  |                                                                                       |                                                                                                                                     |                                    | 1/1         |
| 序号<br>No.         | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE |                  |                                                                                       |                                                                                                                                     |                                    |             |