

C RTP Series Non-lighted Single-pole Rocker Switches

Approvals

UL recognized, CSA certified. Load rating: 20A 125/250 VAC. 1 HP, 125/250 VAC. 14A 14VDC, VDE approval 15A. Contacts: fine silver for long life dependability. Dielectric strength: 1250 volts (live parts to ground). Life: 35,000 operations at maximum rating. Insulation resistance: 5 megohms.

Low Level Control

For low level/dry circuit applications (<100 am) contact factory for part number (Gold plated contacts).

High Inrush

125 Amp inrush capability (AgNi contacts).

Terminals

Style A - 1/4-inch quick-connect

Mechanical Features

100,000 mechanical operations






Markings

Letters, numbers and symbols can be applied to rocker actuator or to integral nylon bezel; see inside back cover for details.

Mounting

Snap-in type panel mounting for ease of installation without additional mounting hardware.

Circuit	Switching	
1	SPST Maintained	
2	SPDT Maintained	
3	SPDT Maintained Center Off	
4	SPST (Momentary) Normally Open	
5	SPDT (Momentary) Normally Closed	
6	SPDT (Momentary) Transfer	
7	SPDT Maintained Center Off (Momentary)	
8	SPDT (Momentary) Center Off (Momentary)	



Panel Cut Out
Panel Thickness 1/32" - 3/16"

Ordering Information:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CW Industries:

[CRTP5A7M9](#) [CRTP8A12M9](#) [CRTP1A9M9-B](#) [CRTP4A7M9](#) [CRTP8A7M9](#) [CRTP4A9M9-B](#) [RTP3A12M9](#)
[RTP4A9M9](#) [RTP1A9M9](#) [CRTP1H9M9](#) [CRTP1A9M9](#) [RTP8A9M9](#) [RTP2A9M9](#) [CRTP6A9M9](#) [RTP8A7M9](#)
[CRTP8A9M9-B](#) [CRTP1A7M9-B](#) [CRTP8A9M9](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CW Industries:

[CRTP1A7M9-B](#) [CRTP1A9M9](#) [CRTP1A9M9-B](#) [CRTP1H9M9](#) [CRTP4A7M9](#) [CRTP4A9M9-B](#) [CRTP5A7M9](#)
[CRTP6A9M9](#) [CRTP8A12M9](#) [CRTP8A7M9](#) [CRTP8A9M9](#) [CRTP8A9M9-B](#) [RTP1A9M9](#) [RTP2A9M9](#) [RTP3A12M9](#)
[RTP4A9M9](#) [RTP8A7M9](#) [RTP8A9M9](#)