

BL653μ Series Bluetooth[®] + 802.15.4 + NFC Modules

RELIABLE BLUETOOTH CONNECTIVITY FOR IOT - JUST A FRACTION OF THE SIZE



Laird Connectivity's latest range of Nordic nRF52833 based modules specifically targets OEMs where space is constrained in their designs. Yet still the **miniaturized BL653µ series** enables Industrial OEMs to robustly implement **longer range** BLE applications in the **harshest operating environments**. This series of secure, low power microcontroller modules with multi wireless capabilities is the future of wireless Internet of Things (IoT) connectivity.

Powered by Nordic's nRF52833 WLCSP silicon, the small form factor BL653µ modules provide for a secure, robust Bluetooth Low Energy and Cortex -M4F CPU for any OEM's product design. The BL653µ provides you with maximum development flexibility with programming options for the Nordic SDK or Zephyr RTOS, a simple, intuitive AT command set, as well as Laird Connectivity's own *smart*BASIC environment.

The BL653µ series brings out key nRF52833 hardware features and capabilities including **USB access**, up to **+8 dBm** transmit power, up to **5.5V** supply considerations, and **NFC tag (type 2 / 4)** implementation. Complete regulatory certifications enable faster time to market and reduced development risk completes Laird Connectivity's simplification of your next small form factor Bluetooth design!

FEATURES AT A GLANCE

TINY FOOTPRINT YET STILL HIGH PERFORMANCE

Nearly 24% reduction in overall module footprint compared to standard BL653 series.



SOFTWARE FLEXIBILITY AND SPEED TO MARKET

Simple AT Command set or easily write event-driven, automated applications, no toolchain required with *smart*BASIC. Alternatively utilize either Zephyr RTOS or the Nordic SDK directly – develop application SW your way

TRUE INDUSTRIAL OPERATING RANGE

Designed and certified to the highest industrial temperature range of -40 °C to +105 °C for every component utilised.

GLOBAL APPROVALS - MAKE YOURSELF AT HOME

Carries several modular FCC, IC, CE, RCM, MIC and Bluetooth SIG approvals.



PERSONAL SUPPORT FROM DESIGN TO MANUFACTURE

Our industry-renowned support is passionate about helping you speed your design to market.

Ultra-small footprint

- o Integrated Antenna (6.3 mm x 8.6 mm x 1.6 mm)
- Trace Pad Option (6.3 mm x 5.6 mm x 1.6mm)
- Bluetooth v5.1 Bluetooth Low Energy (BLE) plus NFC
- 802.15.4 radio (non-certified) –ZigBee / Thread via nRF Connect SDK or Thread via Zephyr)
- Widest range of configurable interfaces: UART, I2C, I2S, SPI, ADC, GPIO, PWM, FREQ, USB, PDM, and NFC
- Extended Industrial Temperature Rating (-40° to +105 °C)
- Bluetooth Low Energy Peripheral/Central roles supported
- 2 Mbps and LE Long Range: Support for 2 Mbps, 1 Mbps, & 125 Kbps coded PHY
- Bluetooth 5.1 Direction finding AoA and AoD
- Hostless operation Internal MCU reduces BOM
- Powerful Core Cortex-M4F (512kB Flash, 128 k RAM)
- Built on years of experience with Nordic (BL600, BL652 & BL654 Series)
- Application design choice: Leverage Laird Connectivity's smartBASIC,
- simple AT command set, Zephyr RTOS or utilize Nordic SDK directly
 Nordic nRF52833 3.175 x 3.175mm WLCSP with 32 GPIOs utilized.





Professional Lighting



Direction Finding / AoA / AoD



Secure Medical Peripherals



Industrial IoT Sensors



BL653µ Series Bluetooth[®] + 802.15.4 + NFC Modules

KEY SPECIFICATIONS

CATEGORY	FEATURE	SPECIFICATION		
Wireless	Bluetooth®	v5.1		
Specification	802.15.4	Thread and Zigbee support via Nordic nRF Connect SDK, Thread via Zephyr		
	Frequency	2.402 - 2.480 GHz		
	Transmit Power	+ 8 dBm (maximum). Configurable down to -40 dBm		
	Receive Sensitivity	-96 dBm (typical @ BLE 1 Mpbs)		
		-103 dBm (typical @ BLE 125 Kbps)		
	Link Budget	103 dB (@ BLE I Mbps), 111 dB (@ BLE 125 Kbps)		
	Antenna Options	Integrated chip antenna or RF trace pin for external antennas		
	Raw Data Rates (Air)	1 Mbps, 2 Mbps, 125 Kbps		
Host Interface and Peripherals	UART Interface	TX, RX, CTS, RTS. DTR, DSR, DCD, RI (GPIO)		
		Default: 115200, N, 8, 1. Configurable from 1200 bps to 1 Mbps		
	USB Interface	USB 2.0 full speed device		
	Other	32 multifunction GPIO's that can provide:		
	0	2 UART (4 GPIO pins each)	1 I2S (5 GPIO pins)	
		8 ADC channels (1 pin each)	2 GPIO pins for 32.768 kHz crystal	
		2 I2C (2 GPIO pins each)	2 GPIO pins for NFC	
		Up to 4 SPI Master / 3 SPI slave with easyDMA	PWM output on 16 pins	
		(4 GPIO pins including CS each)	FREQ output on 16 pins	
		2 UART (4 GPIO pins each)	2 PDM (2 GPIO pins each)	
		8 ADC channels (1 pin each)	1 I2S (5 GPIO pins)	
		2 I2C (2 GPIO pins each)	2 GPIO pins for 32.768 kHz crystal	
		Up to 4 SPI Master / 3 SPI slave with easyDMA	2 GPIO pins for NFC	
		(4 GPIO pins including CS each)	PWM output on 16 pins	
		2 PDM (2 GPIO pins each)	FREQ output on 16 pins	
Koy DLE Footures	Divete eth Levy Freezer			
Key BLE Features	Bluetooth Low Energy	GATT client & GATT server – Any	LE advertising extensions	
		adopted/custom services	LE secure connections	
		Central/Peripheral roles	Data packet length extensions	
		Up to 8 BLE connections (<i>smart</i> BASIC)	LE privacy v1.2	
		BLE Mesh – nRFConnect SDK / Zephyr	LE ping	
		CODED PHY	vSP – Virtual Serial Port	
Due energy a la litera	ID A CLO	2M PHY	DTM Firmware (Test Modes) – Built In	
Programmability Options	smartBASIC	On-board BASIC event driven programming language		
	AT Command Set	Simple AT Hayes-style command protocol		
	Nordic nRFConnect SDK	Software/Support available from Nordic directly https://devzone.nordicsemi.com/		
	Zephyr RTOS	Software/Support available from https://www.zephyrproject.org/		
FW upgrade		Via UART or JTAG (SWD)		
Supply Voltage		1.7V – 5.5V		
Power Consumption	Current	Max Peak Radio Current (@ +8 dBm TX) – 14.1 mA (DCDC at 3V)		
		Max Peak Radio Current (@ 0 dBm TX) – 4.9 mA (DCDC at 3V)		
		Standby Doze – 2.6 μA		
		Deep Sleep –0.6 μA (external signal wake-up)		
Physical	Dimensions	6.3 mm x 8.6 mm x 1.6mm (Integrated Antenna), 6.3 mm x 5.6 mm x 1.6mm (Trace Pad variant)		
Environmental	Temp Range	-40°C to +105°C		
	Lead Free	Lead-free and RoHS-compliant		
		None available – utilise larger BL653 DVK – part # 453-00039-K1 or 453-00041-K1		
	Development Kit	None available – utilise larger BL653 DVK – part	# 453-00039-K1 or 453-00041-K1	
Miscellaneous Development Tools				
Miscellaneous	Development Kit	None available – utilise larger BL653 DVK – part UwTerminalX and UWFlashX (Multi-platform), N Complete Declaration ID		

For full specifications on BL653 modules, please see the appropriate datasheet.

PART #	DESCRIPTION
453-00059R	BL653µ - Micro Bluetooth Low Energy module (Nordic nRF52833) – Integrated antenna (Tape/Reel)
453-00060R	BL653μ - Micro Bluetooth Low Energy module (Nordic nRF52833) – Trace pin (Tape/Reel)
453-00059C	BL653µ - Micro Bluetooth Low Energy module (Nordic nRF52833) – Integrated antenna (Cut Tape)
453-00060C	BL653μ - Micro Bluetooth Low Energy module (Nordic nRF52833) – Trace pin (Cut Tape)