

COAXIAL ADAPTER, UHF, X Ohm, jack / jack (female / female)

31_UHF-0-0-1/022_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
UHF	jack (female)	IEC 60169-12
UHF	jack (female)	IEC 60169-12

Interface and material data

UHF		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PP (Polypropylene)	
UHF		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PP (Polypropylene)	

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0202 kg
Mating cycles	500

Environmental data

Operation temperature	-25 °C ... 100 °C
-----------------------	-------------------

COAXIAL ADAPTER, UHF, X Ohm, jack / jack (female / female)
31_UHF-0-0-1/022_-

Ordering Information Table		
Item number	Item description	Packaging type
22542810	31_UHF-0-0-1/022_-E	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2358 / Date of publication: 27.05.2024 / uncontrolled copy