


REVISION Y

NOTES:

1. © REPRESENTS A CRITICAL DIMENSION.
2. ASSEMBLE GOLD PLATED END AS SHOWN.
3. TERMINAL PUSHOUT FORCE: 2 lbs BEFORE HEAT.
4. TERMINALS TO BE FLUSH TO .010[.25] BELOW TOP OF SHROUD.

DO NOT
SCALE FROM
THIS PRINT



HTST-1XX-01-XX-DV-XX-XX

PACKAGING OPTION

-TR: TAPE & REEL
(POSITIONS -02 THRU -25 ONLY)

OPTION

- A: ALIGNMENT PIN (* ASO OPTION)
(SEE FIG. 3 SHT. 2)
- P: PICK & PLACE PAD
(USE PPP-22)
- XX: POLARIZATION OPTION
(INDICATES POSITION OMITTED)

PLATING SPECIFICATION

- (VALUES GIVEN ARE IN MICRO-INCHES)
- T: MATTE TIN, CONTACT AND TAIL
 - S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL
 - L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL
 - H: HEAVY GOLD, 30 Au / 50 Ni MIN ON CONTACT,
3 Au / 50 Ni MIN ON TAIL
 - F: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL
 - TM: MATTE TIN CONTACT AND TAIL
 - SM: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL
 - FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL
 - LM: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT,
MATTE TIN TAIL

ROW SPECIFICATION

- DV: DOUBLE VERTICAL
(USE HTST-XX-D)







TABLE 1	
POSITIONS	COPLANARITY
-02 THRU -15	.0040[.102]
-16 THRU -36	.0060[.152]



IN-PROCESS VIEW 1



IN-PROCESS VIEW 2



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

INSULATOR:
LCP, UL 94 VO
COLOR: NATURAL

TERMINAL: PHOS BRONZE

c:\enterprise\val\DWG\MISC\MKTG\HTST-1XX-01-XX-DV-XX-XX-MKT.SLDDRW

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

HIGH TEMP TOP SHROUD

DWG. NO.

HTST-1XX-01-XX-DV-XX-XX

BY: T. WERNE 07/11/2001

SHEET 1 OF 3




FIG. 2

-P: PICK & PLACE PAD OPTION
(SAME AS FIG. 1 UNLESS OTHERWISE STATED)




FIG. 3

-A: ALIGNMENT PIN OPTION
(SAME AS FIG. 1 UNLESS OTHERWISE STATED)

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

HIGH TEMP TOP SHROUD



DWG. NO.

HTST-1XX-01-XX-DV-XX-XX

BY: T. WERNE

07/11/2001

SHEET 2 OF 3




SECTION "B"-B"
SCALE 1 : 1

USER DIRECTION OF REELING →
POCKET NOT DETAILED

TAPE & REEL VIEW

TUBE VIEW



TUBE: PT-1-24-02-08
PLUG: TP-13

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

HIGH TEMP TOP SHROUD

DWG. NO.

HTST-1XX-01-XX-DV-XX-XX

BY: T. WERNE

07/11/2001

SHEET 3 OF 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HTST-108-01-TM-DV-P](#) [HTST-112-01-L-DV-A](#) [HTST-108-01-F-DV-P-TR](#) [HTST-120-01-F-DV-A](#) [HTST-113-01-F-DV-](#)
[A](#) [HTST-104-01-F-DV-A-TR](#) [HTST-115-01-L-DV-P](#) [HTST-107-01-H-DV-A](#) [HTST-110-01-SM-DV-A-TR](#)