

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2125280601

Status:


Active

Overview:

Micro-Fit+ Connector System

Description:

Micro-Fit+ Right-Angle Header, 3.00mm Pitch, Dual Row, 6 Circuits, 0.38µm Gold (Au) Plating, UL 94V-0, Glow-Wire Capable, Black



Documents:

[Drawing \(PDF\)](#)

[Product Specification 2064600000-PS-000 \(PDF\)](#)

[Packaging Specification 2125280000-PK-000 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	PCB Headers
Series	212528
Application	Power, Wire-to-Board
Footprint Viewer	Yes
Overview	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	193264256464
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.946/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Plating min - Mating	0.381µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2125280000-PK-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
212528 Series

Mates With
Micro-Fit+ Receptacle [206461](#)

This document was generated on 09/11/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION