

COAXIAL CONNECTOR, 4.3-10, 50 Ohm, Straight cable jack (female)

21_4310-50-3-1/003_-

Properties

- Excellent PIM and RL independent of torque
- Compact size (25.4mm flange)
- Applicable in frequencies up to 12 GHz
- 40% lower weight and size than 7/16
- IEC Standardized

**Product configuration**

Interface type	Gender	Standard
4.3-10	jack	IEC 61169-54

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	Silver Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data

Impedance	50 Ω
Interface frequency	12 GHz

Mechanical data

Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data

Operation temperature	-55 °C ... 90 °C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
85068552	21_4310-50-3-1/003_-Y	Tray

COAXIAL CONNECTOR, 4.3-10, 50 Ohm, Straight cable jack (female)
21_4310-50-3-1/003_-

Suitable cables	
Cable group	Y5 - 3 mm / 50 Ohm
	Y17 - 3 mm / 50 Ohm
	Y12 - 3 mm / 50 Ohm
Suitable cables	SUCOFORM_141
	MULTIFLEX_141
Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2942 / Date of publication: 25.11.2023 / uncontrolled copy