



DDR-15-xxP



DDR-15-xxST



DDR-15-xxDR



Features

- 150~1500Vdc 10:1 ultra-wide input range
- 4KVac I/O high isolation(Reinforced isolation)
- Protections: Short circuit / Overload / Over voltage /
DC input under voltage / DC input reverse Polarity
- Fanless design, fully encapsulated, cooling by free air convection
- Can be installed on DIN rail TS-35/7.5 or 15 (DR-Type)
- -40~+80°C ultra-wide operating temperature (> +50°C derating)
- Operating altitude up to 5000 meters
- 3 years warranty

Applications

- Photovoltaic power generation
- Renewable Energy System
- High voltage frequency conversion
- Industrial control system
- Semiconductor fabrication equipment
- Electro-mechanical apparatus
- DC bus centralized application
- Energy storage system(ESS)
- Charging pile
- Third rail

GTIN CODE

MW Search: <https://www.meanwell.com/serviceGTIN.aspx>

Description

DDRH-15 series is a 150 ~ 1500Vdc high reliable ultra-high input DC-DC converter which can supply stable working voltage for the load. Main features are as following: compact size, -40~+80°C wide range operating temperature, 4KVac high isolation voltage, operation at 5000m altitude, low ripple & noise, complete protections and so on. Furthermore, this series also has DIN Rail type, it is suitable to be mounted on TS-35/7.5 or TS-35/15 rails. DDRH-15 is designed to meet UL1741(By requested) and IEC62109-1 standard. It is suitable for industrial automation, surveillance, telecommunication and can be widely deployed in the applications of new energy generation such as solar power, and windmill power generation, for instances, photovoltaic power systems, high voltage inverting , DC bus centralized application, ESS, charging pile, railway and so forth.

Model Encoding

DDRH - 15 - 12 P

{ P : PCB mounting type
 ST: Screw terminal type
 DR: DIN rail type

Output voltage (5V/12V/15V/24V)

Rated wattage

Series name



15W High Reliable 150~1500Vdc Ultra Wide Input DC-DC Converter


DDRH-15 series

MODEL SELECTION TABLE							
ORDER NO.	INPUT			OUTPUT		EFFICIENCY (Typ.)	CAPACITOR LOAD (MAX.)
	INPUT VOLTAGE (RANGE)	INPUT CURRENT		OUTPUT VOLTAGE	OUTPUT CURRENT		
		NO LOAD	FULL LOAD				
DDRH-15-05 <input type="checkbox"/>	Nominal 800Vdc (150~1500Vdc)	0.2mA	25mA	5V	2A	78%	2000μF
DDRH-15-12 <input type="checkbox"/>		0.2mA	30mA	12V	1.25A	79%	1250μF
DDRH-15-15 <input type="checkbox"/>		0.2mA	30mA	15V	1A	87%	1000μF
DDRH-15-24 <input type="checkbox"/>		0.2mA	30mA	24V	0.625A	88%	625μF

☐ = P, ST, DR

SPECIFICATION					
INPUT	VOLTAGE RANGE		150 ~ 1500Vdc		
	FILTER		Pi type		
	EXTERNAL INPUT FUSE		4A/1500Vdc, required (Please refer to page 6 for more details)		
	INRUSH CURRENT (Typ.)		Cold start 150A max. @ Vin=800Vdc		
OUTPUT	VOLTAGE ACCURACY		± 2.0%		
	RATED POWER		5Vo: 10W 12Vo ~ 24Vo: 15W		
	RIPPLE & NOISE Note.2		5 ~ 15Vo: 100mVp-p 24Vo: 150mVp-p		
	LINE REGULATION		± 1%		
	LOAD REGULATION		± 1% (10% Load to Full Load)		
	SWITCHING FREQUENCY (Typ.)		25 ~ 75.6KHz		
	HOLD UP TIME		16ms min. @Vin=800Vdc		
	SETUP TIME		1s max. @150~1500Vdc		
PROTECTION	SHORT CIRCUIT		Protection type : Hiccup mode, continuous, automatic recovery		
	OVERLOAD		110 ~ 300% rated output power		
			Protection type : Hiccup mode, recovers automatically after fault condition is removed		
	OVER VOLTAGE		Hiccup mode, recovers automatically after fault condition is removed		
	DC INPUT	REVERSE POLARITY		By internal Bridge Diode, no damage, recovers automatically after fault condition removed	
		UNDER VOLTAGE LOCKOUT	Start-up voltage		147Vdc
Shutdown voltage			137Vdc		
ENVIRONMENT	WORKING TEMP.		-40 ~ +80℃ (Refer to "Derating Curve")		
	WORKING HUMIDITY		20% ~ 90% RH non-condensing		
	STORAGE TEMP., HUMIDITY		-40 ~ +85℃, 10 ~ 95% RH non-condensing		
	TEMP. COEFFICIENT		± 0.02% / °C (0 ~ 50℃)		
	VIBRATION		Component: 10 ~ 500Hz, 3G 10min./1cycle, 60min. each along X, Y, Z axes; Mounting clip: Compliance to IEC60068-2-6		
	OPERATING ALTITUDE Note.3		5000 meters		
	OVER VOLTAGE CATEGORY		II ; According to EN62109-1; altitude up to 5000 meters		
	SAFETY & EMC (Note.4)	SAFETY STANDARDS		IEC62109-1(LVD), EAC TP TC 004 approved; Design refer to UL1741(By requested)	
WITHSTAND VOLTAGE		I/P-O/P:4KVac			
ISOLATION RESISTANCE		I/P-O/P, 100M Ohms / 500VDC / 25℃ / 70% RH			
EMC EMISSION		Parameter		Standard	
		Conducted		BS EN/EN55032	
		Radiated		BS EN/EN55032	
EMC IMMUNITY		BS EN/EN55035			
		Parameter		Standard	
		ESD		BS EN/EN61000-4-2	
		Radiated Susceptibility		BS EN/EN61000-4-3	
		EFT/Bursts		BS EN/EN61000-4-4	
		Surge		BS EN/EN61000-4-5	
		Conducted		BS EN/EN61000-4-6	
	OTHERS	MTBF		388Khrs MIL-HDBK-217F(25℃)	
DIMENSION (L*W*H)		P Type: 76.2*50.8*25mm, ST Type: 122.3*57.3*32mm, DR Type: 122.3*57.3*43.5mm			
CASE MATERIAL		Non-conductive black plastic (UL 94V-0 rated)			
POTTING MATERIAL		UL 94V-0			
PIN MATERIAL		Base: copper, Plating: Matte Tin			
PACKING		P Type : 170g ; 6pcs/Tray, 18pcs/per carton ST Type : 210g ; 6pcs/Tray, 18pcs/per carton DR Type : 215g ; 6pcs/Tray, 18pcs/per carton			
NOTE	1. All parameters NOT specially mentioned are measured at 800Vdc input, rated load and 25℃ of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1µf & 47µf parallel capacitor. 3. The ambient temperature derating of 3.5℃/1000m with fanless models and of 5℃/1000m with fan models for operating altitude higher than 2000m(6500ft). 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) ※ Product Liability Disclaimer : For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx				


Derating Curve



Mechanical Specification

- All dimensions in mm(inch)
 - Tolerance: $x.x \pm 0.7\text{mm}$ ($x.x \pm 0.0275"$)
 - $x.xx \pm 0.5\text{mm}$ ($x.xx \pm 0.02"$)
 - $x.xxx \pm 0.5\text{mm}$ ($x.xxx \pm 0.02"$)
- Pin size is: $\phi 1.2 \pm 0.1\text{mm}$ ($\phi 0.047 \pm 0.004$ inch)


DDRH-15-xxP (PCB Mounting Type)



Plug Assignment

Pin-Out	
Pin No.	Output
1	-Vin
2	+Vin
3	NC
4	-Vout
5	+Vout

DDRH-15-xxST (Screw Terminal Type)




Terminal Pin No. Assignment

Pin-Out		
Pin No.	Output	Mating wire
1	-Vin	12~24AWG
2	NC	
3	+Vin	
4	+Vout	
5	-Vout	

Note: Recommended torque setting for terminal is 5kgf-cm(4.4 Lb-in)

DDRH-15-xxDR (DIN Rail Type)




Terminal Pin No. Assignment

Pin-Out		
Pin No.	Output	Mating wire
1	-Vin	12~24AWG
2	NC	
3	+Vin	
4	+Vout	
5	-Vout	

Note: Recommended torque setting for terminal is 5kgf-cm(4.4 Lb-in)


Installation Instruction(DDRH-15-xxDR only)



ADMISSIBLE DIN-RAIL: TS35/7.5 or TS35/15
(For reference only. Not included with unit.)

EMC Suggestion Circuit

※EMI test standard: BS EN/EN55032 Class A conducted and radiated emission are as below:




Model No.	BS EN/EN55032 Class A			
	Fuse	L1,L2	C1,C2	R1,R2
DDRH-15-xxP	4A/1500Vdc	Common choke 25mH SQ1212	0.33μF/1500Vdc	1/2W 3M, ≥800V
DDRH-15-xxST				
DDRH-15-xxDR				

External Fuse Wiring Instruction


External FUSE is required.FUSE specification:4A/1500Vdc.


Suggested model:

Fuse Brand	Manufacturer Part NO.		MW's Order NO.
	Fuse	Fuse Holder	Fuse + Fuse Holder
WalterFuse	WJ30-4	WJ30-H	WJ30-4_WJ30-H



■ Packing

Standard Packing	DDRH-15-xxP			
	MPQ Per Tray(PCS)	One Tray G.W.	Max. Q'TY/ Carton(PCS)	One Carton G.W.
Unit : mm  <p>DDRH-15-xxP</p> <p>Antistatic Plastic blister</p> <p>Antistatic Plastic blister</p> <p>Antistatic Foam</p> <p>CARTON L400x W320 x H225</p>	6	1.2Kg	18	4.6Kg

Standard Packing	DDRH-15-xxST			
	MPQ Per Tray(PCS)	One Tray G.W.	Max. Q'TY/ Carton(PCS)	One Carton G.W.
Unit : mm  <p>DDRH-15-xxST/DDRH-15-xxDR</p> <p>Antistatic Plastic blister</p> <p>Antistatic Plastic blister</p> <p>Antistatic Foam</p> <p>CARTON L400x W320 x H225</p>	6	1.43Kg	18	5.3Kg
	DDRH-15-xxDR			
	MPQ Per Tray(PCS)	One Tray G.W.	Max. Q'TY/ Carton(PCS)	One Carton G.W.
	6	1.46Kg	18	5.4Kg

■ Installation Manual

Please refer to : <http://www.meanwell.com/manual.html>